

30 Years of Experience
and Innovation

With STL...

Best in Breed PDUs

Product Innovation Leader

Award Winning Power
Management Solutions

Dedicated Customer Support

97% of Our Customers Buy
From Us Again and Again



Server Technology
Quality Rack Power Solutions

**HEADQUARTERS
NORTH AMERICA**

Server Technology
1040 Sandhill Drive
Reno, NV 89521
United States
Tel: +1.775.284.2000
Fax: +1.775.284.2065
sales@servertech.com
www.servertech.com
www.servertechblog.com

**WESTERN EUROPE,
MIDDLE EAST & AFRICA**

Server Technology
Fountain Court
2 Victoria Square
Victoria Street
St. Albans, AL1 3TF
United Kingdom
Tel: +44 (0) 1727 884676
Fax: +44 (0) 1727 220815
salesint@servertech.com

**CENTRAL EUROPE,
EASTERN EUROPE & RUSSIA
NIEDERLASSUNG DEUTSCHLAND**

Server Technology
42119 Wuppertal
Germany
Tel: +49 202 693917 x0
Fax: +49 202 693917-10
salesint@servertech.com

APAC

Server Technology
Room 2301, 23/F, Future Plaza
111-113 How Ming Street,
Kwun Tong, Hong Kong
Tel: +852 3916 2048
Fax: +852 3916 2002
salesint@servertech.com



Stay Powered



Be Supported



Get Ahead

From Your Power Strategy Experts

CDU® Power Cords Plug & Connector Power Cord Options for CDUs											
Plug		Connector		Type	Length	Voltage	Amps	Part#	Description		
BS 1363	 	C19	 	Standard	10' 3m	250V	13A	PTCORD-L4	BS 1363 (UK) to Locking IEC 60320 C19; Fused, EU Approved		
CEE 7/7	 	C19	 	Standard	10' 3m	250V	16A	PTCORD-L2	CEE 7/7 Schuko to Locking IEC 60320 C19; EU Approved		
60309	 	C19	 	Standard	10' 3m	250V	16A	PTCORD-L3	IEC 60309 to Locking IEC 60320 C19; EU Approved		
5-15P	 	C19	 	Standard	10' 3m	125V	15A	PTCORD-L5	NEMA 5-15P to Locking IEC 60320 C19; UL & CSA Approved		
5-20P	 	C19	 	Standard	10' 3m	125V	20A	PTCORD-L6	NEMA 5-20P to Locking IEC 60320 C19; UL & CSA Approved		
L5-20P	 	C19	 	Standard	10' 3m	125V	20A	PTCORD-L7	NEMA L5-20P to Locking IEC 60320 C19; UL & CSA Approved		
L6-20P	 	C19	 	Standard	10' 3m	250V	20A	PTCORD-L1	NEMA L6-20P to Locking IEC 60320 C19; UL & CSA Approved		
C20	 	C19	 	Standard	6' 1.8m	250V	16A	PTCORD-D8	Locking IEC 60320 C20 to Locking C19; UL & CSA Approved		
C14	 	5-15R	 	Standard	1' .31m	125V	10A	CAB-1305	IEC 60320 C14 to NEMA 5-15R; UL & CSA Approved		
5-15P	 	C13	 	Standard	1.5' .45m	125V	10A	CAB-1301D	NEMA 5-15P to IEC 60320 C13; UL & CSA Approved		
5-15P	 	C13	 	Standard	3' .9m	125V	10A	CAB-1301C	NEMA 5-15P to IEC 60320 C13; UL & CSA Approved		
5-15P	 	C13	 	Standard	6' 1.8m	125V	10A	CAB-1301A	NEMA 5-15P to IEC 60320 C13; UL & CSA Approved		
AS 3112	 	C19	 	Special Order	8.2' 2.5m	250V	15A	CAB-1342	Australia/New Zealand AS3112 to IEC 60320 C19; SAA Approved		
BS 546	 	C19	 	Special Order	8.2' 2.5m	250V	16A	CAB-1345	Old British Std. (India/S. Africa) BS 546 to IEC 60320 C13; SABS Approved		
CEI 23-16	 	C19	 	Special Order	8.2' 2.5m	250V	16A	CAB-1361	Italy CEI 23-16 to IEC 60320 C19		
GB 2099	 	C19	 	Special Order	10' 3m	250V	16A	CAB-1362A	China GB2099 to IEC 60320 C19		
GB 2099	 	C19	 	Special Order	8.2' 2.5m	250V	16A	CAB-1362B	China GB2099 to IEC 60320 C19		
IRAM 2073	 	C19	 	Special Order	8.2' 2.5m	250V	10A	CAB-1364	Argentina IRAM 2073 to IEC 60320 C19; IRAM Approved		
JIS 8303	 	C19	 	Special Order	8' 2.4m	125V	15A	CAB-1365	Japan JIS 8303 to IEC 60320 C19; PSE Approved		
SEV 1011	 	C19	 	Special Order	8.2' 2.5m	250V	16A	CAB-1366	Switzerland SEV1011 to IEC 60320 C19		
SI32	 	C19	 	Special Order	8.2' 2.5m	250V	16A	CAB-1363	Israel SI32 to IEC 60320 C19		
6-20P	 	C19	 	Special Order	8' 2.4m	250V	20A	CAB-1354	NEMA 6-20P to IEC 60320 C19		
5-15P	 	C19	 	Special Order	8' 2.4m	125V	15A	CAB-1313	NEMA 5-15P to IEC 60320 C19; UL & CSA Approved		
Blunt Cut		C19	 	Special Order	20' 6.1m	—	—	CAB-1339	IEC 60320 C19 molded to 3-wire bare, 20'; UL & CSA Approved (Call before ordering. Custom length cord using a mechanically attached plug body)		