

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION







THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

| REVISION HISTORY | | | | |
|------------------|-----|----------------|-----------|----------|
| ZONE | REV | DESCRIPTION | DATE | APPROVED |
| - | 1 | INITIAL DESIGN | 8/23/2018 | CWD/RG |

NOTES:
 1. DIMENSIONS ARE IN MILLIMETERS AND [] ARE IN INCHES.



| | |
|---|---|
| TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .5 .XX = ± .30 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° | UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2009 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER FINISH |
| | DO NOT SCALE DRAWING THIRD ANGLE PROJECTION |
| SYMBOLS (Q#) = CRITICAL DIM. (#) = COSMETIC SURFACE | MATERIAL: FINISH: |

SERVER TECHNOLOGY, INC. 

1040 Sandhill Road, Reno, NV 89521

DRAWING TITLE:
OUTLINE DRAWING, SWITCHED POPS, H12

| | | | |
|-------------|-----------|-------------|--------------|
| SIZE | CAGE CODE | DWG NO. | REV |
| B | 049V0 | 412-1291-10 | 1 |
| SCALE: NONE | | | SHEET 1 OF 1 |