



# Power Cords and Cables

## Table of Contents

C19 Connector .....	2 - 6
C13 Connector .....	7 - 8
5-15R Connector .....	9



## Overview

Server Technology, a brand of Legrand, delivers off the shelf and custom power solutions for the data center industry. This data sheet details the range of power cord options available from Server Technology for connecting IT equipment to our power distribution units (PDUs).

Can't find what you're looking for? Please give us a call at 800-835-1515, or contact your authorized Server Technology reseller.

# C19 Connector

## PTCORD-L1





**PLUG**  
L6-20P

**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10'   3m	250V	20A	NEMA L6-20P to Locking IEC 60320 C19; UL & CSA Approved

## PTCORD-L2



**PLUG**  
CEE 7/7


**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10'   3m	250V	16A	CEE 7/7 Schuko to Locking IEC 60320 C19; EU Approved




# C19 Connector

## PTCORD-L3




**PLUG**  
60309




**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10'   3m	250V	16A	IEC 60309 to Locking IEC 60320 C19; EU Approved

## PTCORD-L4



**PLUG**  
BS 1363





**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10'   3m	250V	13A	BS 1363 (UK) to Locking IEC 60320 C19; Fused, EU Approved



# C19 Connector

## PTCORD-L5






**PLUG**  
5-15P

**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10'   3m	125V	15A	NEMA 5-15P to Locking IEC 60320 C19; UL & CSA Approved

## PTCORD-L6



**PLUG**  
5-20P


**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10'   3m	125V	20A	NEMA 5-20P to Locking IEC 60320 C19; UL & CSA Approved




# C19 Connector

## PTCORD-L7




**PLUG**  
L5-20P




**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10'   3m	125V	20A	NEMA L5-20P to Locking IEC 60320 C19; UL & CSA Approved

## PTCORD-D8



**PLUG**  
C20





**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	6'   1.8m	250V	16A	Locking IEC 60320 C20 to Locking C19; UL & CSA Approved



# C19 Connector

## CAB-1354





**PLUG**  
6-20P

**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Special Order	8'   2.4m	250V	20A	NEMA 6-20P to IEC 60320 C19

## CAB-1313



**PLUG**  
5-15P


**CONNECTOR**  
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Special Order	8'   2.4m	125V	15A	NEMA 5-15P to IEC 60320 C19; UL & CSA Approved





# C13 Connector

## CAB-1301A




**PLUG**  
5-15P





**CONNECTOR**  
C13

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	6'   1.8m	125V	10A	NEMA 5-15P to IEC 60320 C13; UL & CSA Approved

## CAB-1301C



**PLUG**  
5-15P




**CONNECTOR**  
C13

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	3'   .9m	125V	10A	NEMA 5-15P to IEC 60320 C13; UL & CSA Approved





# C13 Connector

CAB-1301D



**PLUG**  
5-15P



**CONNECTOR**  
C13

## SPECIFICATIONS




Type	Length	Voltage	Amps	Description
Standard	1.5'   .45m	125V	10A	NEMA 5-15P to IEC 60320 C13; UL & CSA Approved





# 5-15R Connector

CAB-1305



**PLUG**  
C14

**CONNECTOR**  
5-15R

## SPECIFICATIONS

Type	Length	Voltage	Amps	Description
Standard	1'   .31m	125V	10A	IEC 60320 C14 to NEMA 5-15R; UL & CSA Approved



## About Server Technology®

Server Technology, a brand of Legrand, is leading the engineering and manufacturing of customer-driven, innovative and exceptionally reliable power, access and control solutions for monitoring and managing critical IT assets for continual availability.

Server Technology's power strategy experts are trusted to provide Rack PDU solutions for data centers worldwide ranging from small technology startups to Fortune 100 powerhouses. Because power is all we do, Server Technology can be found in the best cloud and colocation providers, forward thinking labs, and telecommunications operations.

Server Technology customers consistently rank us as providing the highest quality PDUs, the best customer support, and most valuable innovation. We have over 12,000 PDU configurations to fit every data center need and most of our PDUs are shipped within 10 days.



### Rack PDU Buying Guide

Find the best PDU for your data center

[servertech.com/rack-pdu-buying-guide](http://servertech.com/rack-pdu-buying-guide)



### Rack PDU Selector

Over 2000 standard configurations


[servertech.com/product-selector](http://servertech.com/product-selector)



### Build Your Own PDU

Build an HDOT or HDOT Cx PDU in 4 easy steps

[byopdu.servertech.com](http://byopdu.servertech.com)



### Speak to a Power Expert

Get free technical support

[servertech.com/support](http://servertech.com/support)



### How to Buy

Tools to simplify the PDU buying process

[servertech.com/how-to-buy](http://servertech.com/how-to-buy)



### About Us

Stay Powered, Be Supported, Get Ahead

[servertech.com/about-us](http://servertech.com/about-us)

1-800-835-1515  
[sales@servertech.com](mailto:sales@servertech.com)  
[www.servertech.com](http://www.servertech.com)

**Server  
Technology®**  
A brand of **legrand**