



Power Cords and Cables

Table of Contents

C19 Connector 2-5



Overview

Server Technology, a brand of Legrand, delivers off the shelf and custom power solutions for the data center industry. This data sheet details the range of power cord options available from Server Technology for connecting IT equipment to our power distribution units (PDUs).

Can't find what you're looking for? Please give us a call at 800-835-1515, or contact your authorized Server Technology reseller.

C19 Connector

PTCORD-L1





PLUG
L6-20P

CONNECTOR
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10' 3m	250V	20A	NEMA L6-20P to Locking IEC 60320 C19; UL & CSA Approved

PTCORD-L2



PLUG
CEE 7/7


CONNECTOR
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10' 3m	250V	16A	CEE 7/7 Schuko to Locking IEC 60320 C19; EU Approved




C19 Connector

PTCORD-L3




PLUG
60309




CONNECTOR
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10' 3m	250V	16A	IEC 60309 to Locking IEC 60320 C19; EU Approved

PTCORD-L4



PLUG
BS 1363





CONNECTOR
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10' 3m	250V	13A	BS 1363 (UK) to Locking IEC 60320 C19; Fused, EU Approved



C19 Connector

PTCORD-L5






PLUG
5-15P

CONNECTOR
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10' 3m	125V	15A	NEMA 5-15P to Locking IEC 60320 C19; UL & CSA Approved

PTCORD-L6



PLUG
5-20P


CONNECTOR
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10' 3m	125V	20A	NEMA 5-20P to Locking IEC 60320 C19; UL & CSA Approved




C19 Connector

PTCORD-L7




PLUG
L5-20P




CONNECTOR
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	10' 3m	125V	20A	NEMA L5-20P to Locking IEC 60320 C19; UL & CSA Approved

PTCORD-D8



PLUG
C20



CONNECTOR
C19

SPECIFICATIONS				
Type	Length	Voltage	Amps	Description
Standard	6' 1.8m	250V	16A	Locking IEC 60320 C20 to Locking C19; UL & CSA Approved



About Server Technology®

Server Technology, a brand of Legrand, is leading the engineering and manufacturing of customer-driven, innovative and exceptionally reliable power, access and control solutions for monitoring and managing critical IT assets for continual availability.

Server Technology's power strategy experts are trusted to provide Rack PDU solutions for data centers worldwide ranging from small technology startups to Fortune 100 powerhouses. Because power is all we do, Server Technology can be found in the best cloud and colocation providers, forward thinking labs, and telecommunications operations.

Server Technology customers consistently rank us as providing the highest quality PDUs, the best customer support, and most valuable innovation. We have over 12,000 PDU configurations to fit every data center need and most of our PDUs are shipped within 10 days.



Rack PDU Buying Guide

Find the best PDU for your data center

servertech.com/rack-pdu-buying-guide



Rack PDU Selector

Over 2000 standard configurations

servertech.com/product-selector



Build Your Own PDU

Build an HDOT or HDOT Cx PDU in 4 easy steps

byopdu.servertech.com



Speak to a Power Expert

Get free technical support

servertech.com/support



How to Buy

Tools to simplify the PDU buying process

servertech.com/how-to-buy



About Us

Stay Powered, Be Supported, Get Ahead

servertech.com/about-us

1-800-835-1515
sales@servertech.com
www.servertech.com

**Server
Technology®**
A brand of **legrand**