



P-LOCK

LOCKING POWER CABLES



STOP

ACCIDENTAL DISCONNECTS

Lock down your data center power cords with the P-Lock from Total Cable Solutions. As more manufacturers are offering locking outlets, the P-Lock is quickly becoming the standard to prevent accidental disconnection of power cords from PDU outlets. P-Locks are designed with "P-shaped" clips on each side of the plug housing. These clips produce an audible "click" when inserted assuring a secure locking fit between the plug and the outlet.

P-Locks are available in Black, Blue and Red to easily identify main and redundant power sources at a glance. Color coding with P-Locks adds peace-of-mind and ensures maximum uptime.



FEATURES

- Male connector locks securely into locking PDU
- UL Listed
- Ships coiled, never kinked
- Lifetime Warranty

SPECIFICATIONS

P-Lock C14 to C13

- Electrical Rating: 15 Amp, 250 Volt
- Temperature Rating: to 105° C
- Approvals: UL Listed, RoHS Compliant
- Jacket: SJT, 14 AWG

P-Lock C20 to C19

- Electrical Rating: 20 Amp, 250 Volt
- Temperature Rating: to 105° C
- Approvals: UL Listed, RoHS Compliant
- Jacket: SJT Jacket, 12 AWG

P-Lock C14 to C15

- Electrical Rating: 15 Amp, 250 Volt
- Temperature Rating: to 105° C
- Approvals: UL Listed, RoHS Compliant
- Jacket: SJT Jacket, 14 AWG





TOTAL CABLE SOLUTIONS



Easy pinch design allows quick release from outlets

P-Lock is the only locking cable compatible with new high density Server Technology® HDOT® PDUs

P-tabs ensure that P-Lock cables lock securely into Server Technology® lockable PDUs

P-LOCK

LOCKING POWER CABLES



Feature

SUREFIT™

LOCKING SLEEVE

The SureFIT™ Locking Sleeve creates a strong connection and prevents power cables from being accidentally dislodged. Use SureFIT™ on the female end of your P-Lock Locking Power cable. Available for C13 and C19.



DID YOU KNOW?



• While P-Lock Locking Cables will work in ANY PDU, they are 100% compatible with Server Technology® Lockable PDUs. Tests have shown that P-Locks will lock into other major brands' locking PDUs as well.

*Total Cable Solutions is not affiliated with Server Technology® or their products.

ORDERING INFORMATION

PWR - J - 2 - F

1 2 3 4 5 6 7 8 9

1 FEMALE SIDE **2 MALE SIDE** **3 JACKET TYPE** **4 LABELS** **5 AMPERAGE** **6 VOLTAGE**

C13 = 3
C15 = 5
C19 = 9

C14 = F
C20 = T

SJT = J

YES = L
NO = Blank

15 AMP = 5
20 AMP = 0

250V = 2

7 COLOR **8 LENGTH** **9 UNIT OF MEASURE**

Black = BK
Blue = BL
Red = RD

3-Digit Length
Examples:
001, 0.50, 01.5

Feet = F