





SERVER TECHNOLOGY, INC.
 PROPRIETARY INFORMATION
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC.
 THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION
 OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION
 OF SERVER TECHNOLOGY, INC IS PROHIBITED.
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE
 UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION
 REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

ZONE		REV	DESCRIPTION	DATE	APPROVED
-	1		INITIAL DESIGN	1/9/2013	MAR/VB
-	2		UPDATE TO SHOW NEW BACK COVER DESIGN	5/19/14	ROG/TI

NOTES:
 1. DIMENSIONS ARE IN MILLIMETERS AND [] BRACKETS ARE IN INCHES.



DETAIL A
 SCALE 1:4
 'CXG' EXPANSION UNIT

TOLERANCES <small>(UNLESS OTHERWISE SPECIFIED)</small> LINEAR DIMENSIONS: X = ± .500 XX = ± .200 XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° XX = ± 5° XXX = ± 25°	* INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING THIRD ANGLE PROJECTION
SYMBOLS (G#) - CRITICAL DIM. (S) - COSMETIC SURFACE	MATERIAL: FINISH:

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**OUTLINE DRAWING, SWITCHED PIPS
 V48 (36)C13 (12)C19, 400V 3PH WYE 6BR.
 32A TOP/TOP FRONT ENTRY**

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	412-0729-11	2
SCALE	NONE	SHEET	1 OF 1