



# RACK POWER DISTRIBUTION

PRODUCT CATALOG | NORTH AMERICA

2025

TABLE OF CONTENTS

ABOUT LEGRAND® . . . . . 3

ABOUT SERVER TECHNOLOGY® . . . . . 4

WHY SERVER TECHNOLOGY? . . . . . 5

ADVANCED TECHNOLOGIES . . . . . 6

PER OUTLET POWER SENSING (POPS®) . . . . . 7

PER INLET POWER SENSING (PIPS®) . . . . . 8

PDU FAMILIES . . . . . 10-11

FEATURE HIGHLIGHTS . . . . . 14-16

SWITCHED POPS PDUS . . . . . 17-19

SWITCHED PDUS . . . . . 20-22

SMART POPS PDUS . . . . . 23-25

SMART PDUS . . . . . 26-28

METERED PDUS . . . . . 29-30

BASIC PDUS . . . . . 31-32

-48VDC PDUS . . . . . 33-34

POWER CORDS AND ACCESSORIES . . . . . 35-36

RACK PDU SELECTOR . . . . . 37




## ABOUT LEGRAND

Legrand's Data, Power & Control division delivers an innovative, industry-leading portfolio of expertly engineered solutions that meet the ever-evolving needs of data centers and building network infrastructures.

The businesses that drive digital transformation trust us with their mission-critical operations because of the commitment to technological excellence established by our Ortronics®, Raritan®, Server Technology®, Starline®, Approved Networks®, and ZPE Systems brands. We maintain the problem-solving approach of listening to customers and understanding their requirements before designing and building innovative solutions that deliver a competitive edge for you.

At Legrand, we are committed to developing sustainable solutions that ensure exceptional performance, reducing the environmental impact of our operations, and transforming how people live and work—more efficiently, comfortably, and safely. Sustainable solutions are also innovative solutions. And innovation is at the heart of how we fulfill the needs of our customers.





## ABOUT SERVER TECHNOLOGY

Server Technology is part of Legrand's Data, Power & Control division and is leading the engineering and manufacturing of customer-driven, innovative, and exceptionally reliable power, access, and control solutions for monitoring and managing critical IT assets for continual availability.

Server Technology's power strategy experts are trusted to provide rack power distribution unit (PDU) solutions for data centers worldwide, ranging from small technology startups to Fortune 100 powerhouses. Because power is all we do, Server Technology solutions are found in the best cloud and colocation providers, forward-thinking labs, and telecommunications operations.

Server Technology customers consistently rank us as providing the highest quality PDUs, the best customer support, and the most valuable innovation. We have thousands of PDU configurations to fit every data center's needs. At Server Technology, we pride ourselves on going the extra mile for customers. Whether it's our expert customer support staff talking you through technical needs or our vast library of product documentation, our goal is to help you Stay Powered, Be Supported, and Get Ahead.

## WHY SERVER TECHNOLOGY?



### Stay Powered

#### Reliable, Flexible, and Sustainable Power

Our power strategy experts have pioneered data center power solutions for 40 years.

#### Ensuring Your PDU's Quality & Reliability

We test every PDU and outlet.

#### Setting the Standard for Innovation

We hold the most patents in the industry.



### Performance

#### Acclaimed Service

Customers consistently rank us as providing the best customer support.

#### Delivering Flexibility

We offer the largest PDU selection on the market.

#### Technical Support

Technical support is available from Server Technology's power strategy experts.



### Flourishing

#### Ingenuity-Driven Products

Turning breakthroughs into off-the-shelf solutions.

#### Industry-Renowned Innovations

Multiple awards for industry-leading innovations.

#### Designed for Speed of Deployment

Optimizing our designs to allow faster installations.

**2020 - Data Centre PDU Innovation of the Year - PRO3X PDU Solution**

**2019 - Data Center PDU Innovation of the Year - High Density Outlet Technology (HDOT) Cx Rack Mount PDU**

**2018 - Data Centre PDU Product of the Year - High Density Outlet Technology (HDOT) with Alternating Phase Outlets Rack PDU in Switched and Smart POPS**

**2016 - Data Centre PDU Product of the Year - HDOT Rack Mount PDU in Switched and Smart POPS**

**2014 - Data Center Dynamics North America Innovator Finalist - HDOT**

## LIMITLESS POSSIBILITIES, ONE STANDARD PDU

Leaders in rack power distribution units for 40 years, Server Technology Rack PDUs are the preferred choice for a range of data centers, from innovative startups to respected Fortune 100 companies. Our passion is to push the boundaries of Rack PDU technology and deliver groundbreaking innovations in hardware and intelligence.



### PRO4X Rack PDUs

The PRO4X, launched in 2023, builds on generations of existing intelligent rack power distribution technology, and pioneering outlet designs with groundbreaking features. It integrates 40 years of customer-driven technology, experience, and innovation to meet your demanding data center specifications for efficient, robust performance.

### PRO3X Rack PDUs

The PRO3X is the first hybrid PDU featuring flexible HDOT/ HDOT Cx outlets, a new RamLock mechanical locking mechanism, a multi-color LCD with a push-button interface, a fully hot-swappable onboard controller, the Xerus™ Technology Platform, and our high accuracy PIPS/POPS measurement circuitry all combined into a small form factor.



### PRO2® Rack PDUs


The PRO2 features a flexible hardware platform with more outlets, a faster processor, improved firmware, and increased security and redundancy. With PRO2, you can maintain the high availability of your data, stay informed of rising loads, and be proactive in your power supply management.

## PER OUTLET POWER SENSING (POPS®)

POPS is the foremost outlet power measurement technology for data center device-level power monitoring. POPS prepares Smart and Switched PDUs for environments that require high-density computing. A POPS-equipped PDU offers device-level output measurement capability, allowing you to track and manage the cabinet's servers, applications, and IT equipment. With the ability to measure, monitor, and report power down to the rack or outlet level, this solution follows The Green Grid's recommendations for acquiring the most accurate power monitoring data.

### WITH A POPS-EQUIPPED SMART OR SWITCHED PDU YOU CAN:

- Monitor SNMP traps, email alerts, configuration changes, system events, load, temperature, humidity, and much more
- Group outlets across linked PDUs
- Configure many aspects of the rack PDU remotely
- Ping an IP address to see if equipment is responding
- Receive alerts for power, control state, current, power factor, harmonic distortion, and more
- Use open APIs to share device-level power data with other systems in your infrastructure




## PER INLET POWER SENSING (PIPS®)

PIPS is the premier inlet power measurement technology for data center rack-level power monitoring. PIPS technology extends PDU-level power monitoring with higher accuracy and lower cost monitoring of each power circuit attached to a PDU. PIPS enhances Smart and Switched PDUs with the market's most accurate and complete power metrics. Expect the same quality and functionality of an intelligent PDU but with increased data to help you make critical decisions regarding your facility.

### WITH A PIPS-EQUIPPED SMART OR SWITCHED PDU YOU CAN:

- Quickly confirm rack power and environmental conditions as well as monitor metrics regarding current, voltage, power, apparent power, crest factor, reactance, power factor, accumulated energy, voltage dip and swell, and much more.
- Configure outlets, alarms, thresholds, grouping, permissions, email alerts, security settings, communication settings, and SNMP traps
- Use open APIs to share device-level power data with other systems in your infrastructure





## POWER QUALITY MEASUREMENTS

The PRO4X Rack PDU gives real-time insight into critical power quality, energy efficiency, and equipment health. With the most complete and accurate rack power quality monitoring and metrics, you can confidently address capacity planning, environmental optimization, failover planning, and troubleshooting.

The PRO4X's rack-based power quality measurements allow you to proactively troubleshoot sources of power issues like power leaks, distortions, or variations before they become more significant problems. It measures the following types of power quality measurements at the PDU's inlet and/or outlets:

Power Quality Metric	Measurement	Inlet Measurement	Outlet Measurement
Voltage, RMS	VRMS	Y	Y
Voltage, Neutral	VN	Y	N
Voltage, Harmonic Distortion	VTHD	Y	Y
Voltage, Dip & Swell	VDIP VSWL	Y	N
RMS Current	ARMS	Y	Y
Current, Neutral	AN	Y	N
Current, Inrush	AINRUSH	N	Y
Current, Harmonic Distortion	ATHD	Y	Y
Crest Factor	CF	Y	Y
Watts	W	Y	Y
Volt-Amps-Apparent Power	VA	Y	Y
Volt-Amps-Reactive Power	VAR	Y	Y
Power Factor, True	PFtrue	Y	Y
Power Factor, Displacement	PFdisp	Y	Y
Energy	kWh, kVA	Y	Y

*\*Metrics with Y (yes) in the Outlet Measurement column are only available on units equipped with outlet level monitoring. Some model restrictions apply.*

## PDU FAMILIES

### SWITCHED POPS PDUs

Switched POPS PDUs are our most feature-rich family and offer both outlet control and device-level output measurement capabilities, allowing you to measure, monitor, control, and report power down to the outlet/device level. These PDUs combine highly accurate, outlet-level power measurement technology for data center device-level power monitoring, alerting, and on/off/reboot control. With outlet control, gain features like power-up sequencing and smart load shedding.

### SWITCHED PDUs

Switched PDUs offer device-level output measurement capabilities, allowing you to measure, monitor, control, and report power down to the device level. Switched PDUs also feature outlet lock-out, power-up sequencing to reduce power-up inrushes, and optional smart load shedding. These PDUs feature Smart PDU abilities for network access to power and environmental information and give outlet control for the reboot of locked-up devices.

### SMART POPS PDUs

Smart POPS PDUs provide remote access to PDU-level and outlet-level power, PDU status, and environmental monitoring. With POPS, each unit provides measurements for loads (amps), voltage (V), active power (W), apparent power (VA), crest factor, power factor, and energy power consumption. Local input current monitors help users monitor load and properly balance power as equipment is being added to the equipment rack. Additionally, these PDUs feature branch circuit protection and are available in various voltages and amperages.

### SMART PDUs

Smart PDUs offer device-level output measurement capabilities, allowing you to measure, monitor, and report power down to the device level. Smart PDUs feature branch circuit protection and are available in various voltages and amperages. Available in both single- and 3-phase.

## METERED PDUs

Metered PDUs feature auto-flip current displays to help prevent overloads and simplify 3-phase load balancing in high-density cabinets. Optional flexible mounting allows you to mount the PDU in standard or custom brackets. If you're looking for reliable power distribution for the devices in your equipment cabinet, Metered PDUs might be the perfect affordable solution.

## BASIC PDUs

Basic PDUs provide reliable power distribution for the devices in your equipment cabinet, are UL Listed, and meet IEC data center requirements. Basic PDUs are available in single-phase 110-120V or 208-240V power distribution with 20A or 30A options and 3-phase power distribution with 20A and 30A options.



## -48VDC PDUs

-48VDC PDUs control cabinet equipment at remote locations, including colocation facilities and network ops centers, allowing you to reboot locked-up remote servers around the clock. Most models have two DC power input feeds that support dual power networking appliances. Power is distributed to multiple outputs that are individually protected by a fuse or breaker. Each output has current monitoring, allowing you to remotely monitor capacity, utilization, and set up alerts.

## FEATURE HIGHLIGHTS

### HDOT®

Server Technology PDUs with High Density Outlet Technology (HDOT) have the highest outlet count in the smallest form factor, and are the most popular on the market. Available in POPS, Switched, and Smart PDUs, HDOT addresses today's top data center challenges: power density, capacity planning, and remote power management.




### HDOT Cx®


Server Technology's award-winning and patented HDOT technology is enhanced with our Cx Outlet. The Cx outlet is a hybrid of IEC C13 and C19 outlets and accommodates both C20 and C14 power cables in a single outlet. This innovative design reduces the complexity of the PDU selection process while lowering end costs. With HDOT Cx, you won't have to buy a new set of PDUs when equipment changes.

### Alternating Phase Technology

Alternating phase outlets alternate the phased power on a per-outlet basis instead of a per-branch basis allowing for shorter cords, faster installation, and much easier load balancing for 3-phase rackmount PDUs. Shorter cords mean less mass, making them less likely to come unplugged during the transport of the assembled rack or get in the way when servicing the cabinet. In addition, utilizing fewer cables improves airflow, allowing for more efficient cooling.



No Alternating Phase



Alternating Phase



### UNIVERSAL INPUT

The optional Universal Input available on PRO4X PDUs is a one-size-fits-all infeed that accommodates single and 3-phase Legrand Universal Input Cord options for the same PDU.

This unique innovation allows you to purchase a single PDU and swap the input cord to match the power infeed requirements as needed. The PDU's patented plug-and-play EEPROM Smart Cord functionality auto-recognizes newly seated plug and cable ratings, reducing configuration and deployment time.

*The Universal Input must be specified at ordering. It can be added to most PRO4X PDU models. Some restrictions apply. Contact a representative to learn more.*

### CHOOSE THE RIGHT PDU

PDU FAMILY	Branch Circuit Protection	Input Power Monitoring	Individual Outlet Control	Per Outlet Power Monitoring	Enviromental Monitoring	Access, Security & Communications
Switched POPS® PDU	✓	✓	✓	✓	✓	✓
Smart POPS PDU	✓	✓		✓	✓	✓
Switched PDU	✓	✓	✓		✓	✓
Smart PDU	✓	✓			✓	✓
Metered PDU	✓	* ✓				
Basic PDU	✓					

\*Local input current monitoring only  
POPS (Per Outlet Power Sensing)

Please contact your [representative](#) for more information.

## PDU FEATURES

As a leader in product innovation, Server Technology holds many vital patents for providing power in Zero-U and horizontal PDU configurations compatible with today's rack and dense compute infrastructure requirements. Server Technology's advanced features help reduce downtime, facilitate capacity planning, improve energy efficiency, and drive efficiency.












Not all features are listed, and some features are unavailable on select models. Please contact your representative for more information.

	<b>HDOT (HIGH DENSITY OUTLET TECHNOLOGY)</b> The highest outlet density available in a network-connected PDU meets IEC C13 and C19 specifications, plus high native retention and UL94V-0 flame rating.
	<b>HDOT CX OUTLETS</b> The Cx is the future-ready UL tested hybrid of a C13 and C19 outlet accommodating both C14 and C20 plugs.
	<b>ALTERNATING PHASE TECHNOLOGY</b> Evenly distributes multiple phases of power to each outlet for simplified load balancing, reduced cord lengths, and better airflow.
	<b>POPS (PER OUTLET POWER SENSING)</b> Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor, Power Factor, and Energy per outlet.
	<b>OUTLET CONTROL</b> Cycle power to individual outlets or groups of outlets to reboot servers or power off unused receptacles.
	<b>RAMLOCK LOCKING OUTLETS</b> A mechanical locking mechanism built to secure the broadest range of C14 and C20 plugs in place.
	<b>R/G/B LED OUTLET INDICATORS</b> RGB LEDs identify an outlet's on/off state, if it's above/below a certain power threshold, or if it's suspected of a power measurement irregularity.
	<b>BRANCH CIRCUIT PROTECTION</b> This PDU meets the UL and IEC 62368-1 requirement for branch circuit protection through UL 489 rated magnetic-hydraulic circuit breakers or UL 248 fuses.
	<b>45-DEGREE ANGLED INFEEED</b> The angled infeed improves accessibility and provides infeed strain relief. Its bend radius is suitable with 60A rated cords.

## PDU FEATURES

	<p><b>UNIVERSAL INPUT</b></p> <p>A one-size-fits-all universal infeed that accommodates single- and 3-phase Legrand Universal Input cord options for the same PDU, providing flexibility in rack power deployment.</p>
	<p><b>PIPS (PER INLET POWER SENSING)</b></p> <p>Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor, Power Factor, and Energy per inlet.</p>
	<p><b>ADVANCED POWER MONITORING</b></p> <p>Gives real-time insight into power consumption and energy efficiency to improve performance and avoid power quality issues.</p>
	<p><b>BRANCH CURRENT MONITORING</b></p> <p>Monitors current at each breaker branch and provides SNMP-based alerts and emails on high usage that risks a tripped circuit.</p>
	<p><b>POWER QUALITY MEASUREMENTS</b></p> <p>Monitor and alert on the power feeding the PDU for harmonics, voltage dips and swells, crest factor, and more at the outlet or load.</p>
	<p><b>TOTAL HARMONIC DISTORTION</b></p> <p>Monitor harmonic events on the power feeding the PDU or the power distributed to the PDU's outlets or load.</p>
	<p><b>CIRCUIT BREAKER TRIP FORENSICS</b></p> <p>With enhanced circuit breaker trip forensics, identify the specific outlet and device that caused the trip, saving time when investigating and resolving issues.</p>
	<p><b>WAVEFORM CAPTURE</b></p> <p>Capture voltage and current waveforms automatically or on demand.</p>
	<p><b>HOT SWAPPABLE CONTROLLER</b></p> <p>Offers industrial-grade reliability, user-configurable firmware, disaster recovery support, and hot-swappable capability for maintenance or replacement without powering down connected equipment.</p>
	<p><b>MULTI-COLOR LCD</b></p> <p>An easy-to-read display provides a local indication of power usage, alerts, and alarms.</p>
	<p><b>AUTO-FLIP DISPLAY</b></p> <p>Auto-flip display ensures you have the right components in the right visual orientation no matter the PDU's mounting position.</p>

## PDU FEATURES

	<b>DUAL NETWORK CONNECTIONS</b> A modern Gigabit Ethernet port, backed up by a second network connection port, ensures monitoring reliability and allows insights to be shared.
	<b>Multi-Unit Linking &amp; Cascading</b> Cascade 32 PDUs from one ethernet port using bridging mode, or save IP addresses using a single IP address with port forwarding. Use the Link feature for logical connectivity of up to 8 PDUs.
	<b>Environmental Monitoring</b> Supports daisy-chained DX2-series Legrand SmartSensors, each able to send SNMP-based alerts and email notifications.
	<b>USB Mass Configuration</b> A quick and easy solution for PDU configuration and setup.
	<b>IP Access, Security &amp; Communications</b> Web, SSH, Telnet, SNMPv2c & v3, RS-232 serial, 10/100/1000 Base T-Ethernet, LDAP(S), TACACS+, RADIUS, DHCP, and SMTP/email.
	<b>Network Monitoring</b> Gain access to valuable data through connections including HTTP(S), SSH, Telnet, SNMP, (S)FTP, SMTP, Syslog, LDAP(S), and more.
	<b>Advanced Alerting and Intelligence</b> Billing-grade accurate monitoring of user-defined thresholds ensures potential failures are identified in advance. Real-time alarms notify you of possible risk conditions.
	<b>Interoperability</b> Intelligent PDUs provide an open API that interoperates with third-party software such as DCIM or BMS.
	<b>Flexible Mounting</b> Includes standard button mounts along with provisions for custom mounting brackets.
	<b>High-Temperature Rating</b> This product has been tested and approved for safe and reliable operation in 60°C (140°F) environments.
	<b>Color-Coded Options</b> Select from six colors to designate PDU circuits in the data center—black, white, red, green, blue, and yellow.

Learn how the renowned power and revolutionary intelligence of the PRO4X Rack PDU can help you anticipate and meet your rack power challenges. Visit [SERVERTECH.COM/PRO4X](https://SERVERTECH.COM/PRO4X)



## SWITCHED POPS PDUs

Switched POPS Rack PDUs combine outlet power measurement technology for data center device-level power monitoring, alerting, and on/off/reboot control. Use the Switched functionality for cycling power on dual-power IT equipment with one command. With outlet control, gain features like power-up sequencing and smart load shedding.



Blade servers and high-density computing power requirements continue to increase, and POPS is the right PDU for monitoring and managing those environments. POPS, combined with device-level output control, allows you to monitor, track and manage servers, IT equipment, and the equipment cabinet infrastructure.

## POPULAR CONFIGURATIONS

### PRO4X MODEL: C4G36RA-2CBE2FE2

#### 208V Single Phase 30A



Input Power Capacity	5kw
Input Voltage	208V
Input Current	30A
Phase	1-Phase (L-L)
Plug Type	NEMA L6-30P
W x H x D	2.2 x 70 x 2.5 in. (54 x 1778 x 64 mm)
Mounting	0U Vertical
Alternating Phase	No

### PRO2 MODEL: C2WG48TE-DQME2M99

#### 208V 3 Phase Delta 60A



Input Power Capacity	17.3kW
Input Voltage	208V
Input Current	60A
Phase	3-Phase Delta (L-L)
Plug Type	208V Delta 60A IEC 60309 3P+G 9Hr
W x H x D	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)
Mounting	0U Vertical
Alternating Phase	Yes

SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
PRO4X Models									
C4G36RA-0ABE2FE2	36*	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 100-240V Inlet	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4G48RA-0ABE2FD7	36*	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 100-240V Inlet	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4G36RA-2CBE2FE2	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4G48RA-2CBE2FD7	48*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4G36RA-EPBE2FE2	36*	7.3kW	230V	32A	1-Phase (L-N)	IEC 230V/32A 2P+PE 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4G48RA-EPBE2FD7	48*	7.3kW	230V	32A	1-Phase (L-N)	IEC 230V/32A 2P+PE 6Hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4G36RA-DCBE2FE2	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4G48RA-DCBE2FD7	48*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4G36RA-YCBE2FE3	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4G48RA-YCBE2FD8	48*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4G36RA-DFBD2FE1	36*	14.4kW	208V	50A	3-Phase Delta (L-L)	CS8365 3P+G 50A	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4G48RA-DFBD2FD3	48*	14.4kW	208V	50A	3-Phase Delta (L-L)	CS8365 3P+G 50A	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4G36RA-GPBD2FE1	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4G48RA-GPBD2FD3	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4G36RA-YQBD2FE1	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	208V Wye 60A IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4G48RA-YQBD2FD3	48*	17.3kW	230V	60A	3-Phase Wye (L-L)	208V Wye 60A IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4G36RA-DQBD2FE1	36*	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4G48RA-DQBD2FD3	48*	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4G36RA-U6BD2FE1	36*	Up to 22kW	Defined by UIC**	Defined by UIC**	3-Phase Wye (L-L) / 3-Phase Delta (L-L)	Defined by UIC**	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4G48RA-U6BD2FD3	48*	Up to 22kW	Defined by UIC**	Defined by UIC**	3-Phase Wye (L-L) / 3-Phase Delta (L-L)	Defined by UIC**	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes

\*Contains HDOT Cx Outlets, hybrid IEC C13 and C19 outlets that accommodate both C14 and C20 plugs.

\*\*UIC refers to a Legrand Universal Input Cord. Cord options are shown on the Accessories page.

Not all part numbers are listed. Please contact a representative for a full portfolio of options.

## SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
<b>PRO2 Models</b>									
C2WG36TE-2CAF2M66	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2WG36TE-2QAF2M66	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2WG36TE-YCMFAM66	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2WG36TE-DCMFAM66	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2WG36TE-YQME2M66	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2WG48TE-DQME2M99	48*	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2WG36TE-5CAE2M66	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2WG48TE-5PAE2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6Hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2WG24TB-5QCD27T0	24*	34.5kW	415V	60A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6Hr	2.2 x 70 x 3 in. (56 x 2032 x 77 mm)	0U Vertical	No
C2WG24TB-4QCD27T0	24*	43.4kW	400V	63A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6Hr	2.2 x 70 x 3 in. (56 x 2032 x 77 mm)	0U Vertical	No
C2WG08HC-2CBA2DAC	8	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	17.2 x 1.75 x 7 in. (437 x 45 x 178 mm)	1U Horizontal	No
C2WG12SM-2CJA2D3	12*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	17.2 x 1.75 x 11.57 in. (437 x 45 x 294 mm)	1U Horizontal	No
C2WG24SN-DCLN5D6	24*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	17.2 x 3.50 x 17.5 in. (437 x 89 x 445 mm)	2U Horizontal	Yes
C2WG12SM-2CJA2D3	12*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	17.2 x 1.75 x 11.57 in. (437 x 45 x 294 mm)	1U Horizontal	No
C2WG24SN-DCLN5D6	24*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	17.2 x 3.50 x 17.5 in. (437 x 89 x 445 mm)	2U Horizontal	Yes

\*Contains HDOT Cx Outlets, hybrid IEC C13 and C19 outlets that accommodate both C14 and C20 plugs.

Not all part numbers are listed. Please contact a representative for a full portfolio of options.

**Can't find the right PDU? Server Technology has you covered.**



### RACK PDU SELECTOR

Quickly find your PDU

[servertech.com/product-selector](http://servertech.com/product-selector)

## SWITCHED PDUs




Switched Rack PDUs can turn on, off, or reboot outlets individually or as a group. Switched PDUs also feature outlet lock-out and power-up sequencing to reduce power-up inrushes and smart load shedding. These PDUs provide Smart abilities for network access to power and environmental information. Switched PDUs also give outlet control for rebooting of locked-up devices and power-up sequencing.

Switched PDUs are perfect for all environments that require power and environmental monitoring, power-up sequencing, rebooting, and scheduling power loads. These Switched PDUs have been especially useful in rapidly growing environments, such as in colocation facilities. Switched PDUs can be purchased with HDOT Cx and Alternating Phase technology.

### POPULAR CONFIGURATIONS

#### PRO4X MODEL: C4W36RA-5CBD2FE1


##### 415V 3 Phase Wye 30A



Input Power Capacity	17.3kW
Input Voltage	415V
Input Current	30A
Phase	3-Phase Wye (L-N)
Plug Type	NEMA L22-30P
W x H x D	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)
Mounting	0U Vertical
Alternating Phase	Yes

#### PRO2 MODEL: C2W36TE-DQME2M99

##### 208V 3 Phase Delta 60A



Input Power Capacity	17.3kW
Input Voltage	208V
Input Current	60A
Phase	3-Phase Delta (L-L)
Plug Type	208V Delta 60A IEC 60309 3P+G 9H
W x H x D	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)
Mounting	0U Vertical
Alternating Phase	Yes

**SAMPLE CONFIGURATIONS**

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
<b>PRO4X Models</b>									
C4W36RA-0ABE2FE2	36*	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 100-240V Inlet	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4W48RA-0ABE2FD7	48*	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 100-240V Inlet	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4W36RA-2CBE2FE2	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4W48RA-2CBE2FD7	48*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4W36RA-EPBE2FE2	36*	7.3kW	230V	32A	1-Phase (L-N)	IEC 230V/32A 2P+PE 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4W48RA-EPBE2FD7	48*	7.3kW	230V	32A	1-Phase (L-N)	IEC 230V/32A 2P+PE 6Hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4W36RA-DCBE2FE2	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4W48RA-DCBE2FD7	48*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4W36RA-DFBD2FE1	36*	14.4kW	208V	50A	3-Phase Delta (L-L)	CS8365 3P+G 50A	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4W48RA-DFBD2FD3	48*	14.4kW	208V	50A	3-Phase Delta (L-L)	CS8365 3P+G 50A	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4W36RA-YCBE2FE3	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4W48RA-YCBE2FD8	48*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4W36RA-GPBD2FE1	36*	17.3kW 22 kW	415V 400V	30A 32A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4W48RA-GPBD2FD3	48*	17.3kW 22 kW	415V 400V	30A 32A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4W36RA-YQBD2FE1	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	208V Wye 60A IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4W48RA-YQBD2FD3	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	208V Wye 60A IEC 60309 3P+N+G 9Hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4W36RA-DQBD2FE1	36*	17.3kW	415V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4W48RA-DQBD2FD3	48*	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4W36RA-U6BD2FE1	36*	Up to 22kW	Defined by UIC**	Defined by UIC**	3-Phase Wye (L-L) / 3-Phase Delta (L-L)	Defined by UIC**	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4W48RA-U6BD2FD3	48*	Up to 22kW	Defined by UIC**	Defined by UIC**	3-Phase Wye (L-L) / 3-Phase Delta (L-L)	Defined by UIC**	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes

\*Contains HDOT Cx Outlets, hybrid IEC C13 and C19 outlets that accommodate both C14 and C20 plugs.

\*\*UIC refers to a Legrand Universal Input Cord. Cord options are shown on the Accessories page.

Not all part numbers are listed. Please contact a representative for a full portfolio of options.

## SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
PRO2 Models									
C2W36TE-2CAF2M99	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2W36TE-2QAF2M99	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2W42CE-2QAF2M00	42	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C1W24VS-YCFA13C9	24	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	1.75 x 69 x 2.25 in. (45 x 1753 x 58 mm)	0U Vertical	No
C2W36TE-YCMFAM99	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2W42CE-DCMFAM00	42	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2W48TE-DCMFAM99	48*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2W54CE-DCMFAM00	54	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2W36TE-YQME2M99	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2W48TE-YQME2M99	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2W36TE-5CAE2M99	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2W48TE-5CAE2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C1W08HC-2CBA2BAC	8	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.72 x 175 x 7 in. (437 x 445 x 178 mm)	1U Horizontal	No
C1W16HR-2CAA5BAC	16	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.72 x 3.5 x 71 in. (437 x 89 x 181 mm)	2U Horizontal	No
C1W08HC-2CBA2BAC	8	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.72 x 175 x 7 in. (437 x 445 x 178 mm)	1U Horizontal	No
C1W16HR-2CAA5BAC	16	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.72 x 3.5 x 71 in. (437 x 89 x 181 mm)	2U Horizontal	No

\*Contains HDOT Cx Outlets, hybrid IEC C13 and C19 outlets that accommodate both C14 and C20 plugs.  
Not all part numbers are listed. Please contact a representative for a full portfolio of options.

Can't find the right PDU? Server Technology has you covered.



### RACK PDU SELECTOR

Quickly find your PDU

[servertech.com/product-selector](http://servertech.com/product-selector)

## SMART POPS® PDUs

Smart POPS Rack PDUs feature highly accurate, outlet-level power monitoring for your data center power needs. Email alerts provide automated updates on power and environmental conditions. Expansion PDUs may provide full access to all power feeds under a single IP address. SNMP traps and automated email alerts provide consistent insight into your outlet's power levels and surrounding conditions.



With POPS, each unit provides measurements for loads, voltage, active power, apparent power, crest factor, power factor, and energy power consumption. Smart POPS PDUs feature built-in LED current monitors, which feature an Ethernet, serial, and temperature/humidity monitoring port. Optional temperature and humidity probes on 3m (10 ft.) cords allow measurements to be taken in different locations within the cabinet.

### POPULAR CONFIGURATIONS

#### PRO4X MODEL: C4T36RA-DQBD2FE1

##### 208V 3-Phase Delta 60A



Input Power Capacity	17.3kW
Input Voltage	208V
Input Current	60A
Phase	3-Phase Delta (L-L)
Plug Type	208V Delta 60A IEC 60309 3P+G 9Hr
W x H x D	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)
Mounting	0U Vertical
Alternating Phase	Yes

#### PRO2 MODEL: C2SG36TE-DCMFAM66

##### 208V 3 Phase Delta 30A



Input Power Capacity	8.6kW
Input Voltage	208V
Input Current	30A
Phase	3-Phase Delta (L-L)
Plug Type	NEMA L15-30P
W x H x D	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)
Mounting	0U Vertical
Alternating Phase	Yes

## SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
PRO4X Models									
C4T36RA-0ABE2FE2	36*	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 100-240V Inlet	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4T36RA-2CBE2FE2	36*	5kw	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4T36RA-2QBE2FE2	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4T36RA-EPBE2FE2	36*	7.3kW	230V	32A	1-Phase (L-N)	IEC 230V/32A 2P+PE 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4T36RA-EQBE2FE2	36*	11kW	230V	63A	1-Phase (L-N)	IEC 230V/63A 2P+PE 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4T36RA-DCBE2FE2	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4T36RA-YCBE2FE3	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4T36RA-GPBD2FE1	36*	17.3kW 22kW	415V 400V	30A 32A	3-Phase Wye (L-N)	230/400 32A & 240/415V Wye 30A IEC 60309 3P+N+G 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4T36RA-5CBD2FE1	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4T36RA-DFBD2FE1	36*	14.4kW	208V	50A	3-Phase Delta (L-L)	CS8365 3P+G 50A	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4T36RA-DQBD2FE1	36*	17.3kW	208V	60A	3-Phase Delta (L-L)	208V Delta 60A IEC 60309 3P+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4T36RA-YQBD2FE1	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	208V Wye 60A IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4T36RA-U6BD2FE1	36*	Up to 22kW	Defined by UIC**	Defined by UIC**	3-Phase Wye (L-L) / 3-Phase Delta (L-L)	Defined by UIC**	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4T48RA-U6BD2FD3	48*	Up to 22kW	Defined by UIC**	Defined by UIC**	3-Phase Wye (L-L) / 3-Phase Delta (L-L)	Defined by UIC**	2.2 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes

\*Contains HDOT Cx Outlets, hybrid IEC C13 and C19 outlets that accommodate both C14 and C20 plugs.

\*\*UIC refers to a Legrand Universal Input Cord. Cord options are shown on the Accessories page.

Not all part numbers are listed. Please contact a representative for a full portfolio of options.



## SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
<b>PRO2 Models</b>									
C2SG36TE-2CAF2M66	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2SG36TE-2QAF2M66	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2SG36TE-DCMFAM66	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2SG36TE-YCMFAM66	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2SG48TE-YCMFAM99	48*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2SG36TE-YQME2M66	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2SG48TE-DQME2M99	48*	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2SG48TE-YQME2M99	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2SG36TE-5CAE2M66	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2SG48TE-5CAE2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes

\*Contains HDOT Cx Outlets, hybrid IEC C13 and C19 outlets that accommodate both C14 and C20 plugs. Not all part numbers are listed. Please contact a representative for a full portfolio of options.

**Can't find the right PDU? Server Technology has you covered.**



**RACK PDU SELECTOR**

Quickly find your PDU

[servertech.com/product-selector](http://servertech.com/product-selector)

## SMART PDUs




Easy to use and access, Smart Rack PDUs from Server Technology offer input current monitors on easy-to-view LED via network or serial connection. These PDUs feature branch circuit protection and are available in various voltages and amperages. Available in single- and 3-phase.

Smart PDUs are guaranteed secure and feature external authentication and authorization support, while SNMP traps provide automated alerts surrounding each outlet's power and environmental conditions. Optional temperature and humidity probes, with 3m (10 ft.) cords, offer flexibility in terms of sensor placement.

### POPULAR CONFIGURATIONS

#### PRO4X MODEL: C4S48RA-GPBD2FD3

##### 415V 3 Phase Wye 30A



Input Power Capacity	17.3/22kW
Input Voltage	415/400V
Input Current	30/32A
Phase	3-Phase Wye (L-N)
Plug Type	IEC 60309 3P+N+G 6hr
W x H x D	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)
Mounting	0U Vertical
Alternating Phase	Yes

#### PRO2 MODEL: C2S54CE-DQME2M00

##### 208V 3 Phase Delta 60A



Input Power Capacity	17.3kW
Input Voltage	208V
Input Current	60A
Phase	3-Phase Delta (L-L)
Plug Type	208V Delta 60A IEC 60309 3P+G 9Hr
W x H x D	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)
Mounting	0U Vertical
Alternating Phase	Yes

## SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
PRO4X Models									
C4S36RA-0ABE2FE2	36*	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 100-240V Inlet	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4S48RA-0ABE2FD7	48*	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 100-240V Inlet	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4S36RA-2CBE2FE2	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4S48RA-2CBE2FD7	48*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4S36RA-EPBE2FE2	36*	7.3kW	230V	32A	1-Phase (L-N)	IEC 230V/32A 2P+PE 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C4S48RA-EPBE2FD7	48*	7.3kW	230V	32A	1-Phase (L-N)	IEC 230V/32A 2P+PE 6Hr	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	No
C4S36RA-DCBE2FE2	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4S48RA-DCBE2FD7	48*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4S36RA-YCBE2FE3	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4S48RA-YCBE2FD8	48*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4S36RA-DFBD2FE1	36*	14.4kW	208V	50A	3-Phase Delta (L-L)	CS8365 3P+G 50A	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4S48RA-DFBD2FD3	48*	14.4kW	208V	50A	3-Phase Delta (L-L)	CS8365 3P+G 50A	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4S36RA-GPBD2FE1	36*	17.3kW 22 kW	415V 400V	30A 32A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4S48RA-GPBD2FD3	48*	17.3kW 22 kW	415V 400V	30A 32A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6hr	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4S36RA-YQBD2FE1	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	208V Wye 60A IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4S48RA-YQBD2FD3	48*	17.3kW	208V	60A	3-Phase Delta (L-L)	208V Wye 60A IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4S36RA-DQBD2FE1	36*	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4S48RA-DQBD2FD3	48*	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C4S36RA-U6BD2FE1	36*	Up to 22kW	Defined by UIC**	Defined by UIC**	3-Phase Wye (L-L) / 3-Phase Delta (L-L)	Defined by UIC**	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C4S48RA-U6BD2FD3	48*	Up to 22kW	Defined by UIC**	Defined by UIC**	3-Phase Wye (L-L) / 3-Phase Delta (L-L)	Defined by UIC**	2.2 x 80 x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes

\*Contains HDOT Cx Outlets, hybrid IEC C13 and C19 outlets that accommodate both C14 and C20 plugs.

\*\*UIC refers to a Legrand Universal Input Cord. Cord options are shown on the Accessories page.

Not all part numbers are listed. Please contact a representative for a full portfolio of options.

## SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
PRO2 Models									
C2S36TE-2CAF2M99	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2S36TE-2QAF2M99	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2S42CE-2QAF2M00	42	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C2S36TE-DCMFAM99	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2S36TE-YCMFAM99	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2S48TE-YCMFAM99	48*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2S48TE-DCMFAM99	48*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2S36TE-YQME2M99	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2S42CE-YQME2M00	42	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	22 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	Yes
C2S48TE-YQME2M99	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2S54CE-DQME2M00	54	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2S54CE-YQME2M00	54	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2S48TE-5PAE2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6Hr	22 x 80x 2.5 in. (56 x 2032 x 64 mm)	0U Vertical	Yes
C2S24SP-YCLN5D6	24*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	17.2 x 3.5 x 10 in. (437 x 89 x 254 mm)	2U Horizontal	Yes
C2S24SP-DCLN5D6	24*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	17.2 x 3.5 x 10 in. (437 x 89 x 254 mm)	2U Horizontal	Yes
C2S24SP-DCLN5D6	24*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	17.2 x 3.5 x 10 in. (437 x 89 x 254 mm)	2U Horizontal	Yes

\*Contains HDOT Cx Outlets, hybrid IEC C13 and C19 outlets that accommodate both C14 and C20 plugs. Not all part numbers are listed. Please contact a representative for a full portfolio of options.

**Can't find the right PDU? Server Technology has you covered.**



### RACK PDU SELECTOR

Quickly find your PDU

[servertech.com/product-selector](http://servertech.com/product-selector)

## METERED PDUs

Metered Rack PDUs feature auto-flip current displays to help prevent overloads and simplify 3-phase load balancing in high-density cabinets, while optional flexible mounting allows you to mount the PDU in standard or custom brackets. If you're looking for reliable power distribution for all the devices in your equipment cabinet, Metered PDUs might be the perfect affordable solution.



Metered PDUs feature local input current monitoring, which allows you to verify the aggregated load on the outlet's circuit or phase. With branch circuit protection, Metered PDUs are perfect for a range of equipment cabinets, from 2kW-22kW. Available in single-phase 110-120V or 208-240V or 3-phase power distribution with 20A, 30A, 50A, or 60A options.

## POPULAR CONFIGURATIONS

### MODEL: C-12H1B211E7

#### 120V Single Phase 30A



Input Power Capacity	2.8kW
Input Voltage	120V
Input Current	30A
Phase	1-Phase (L-N)
Plug Type	NEMA L5-30P
W x H x D	17.2 x 1.75 x 5 in. (437 x 45 x 127 mm)
Mounting	1U Horizontal
Alternating Phase	No

### MODEL: STV-2001C

#### 208V Single Phase 30A



Input Power Capacity	5kW
Input Voltage	208V
Input Current	30A
Phase	1-Phase (L-L)
Plug Type	NEMA L6-30P
W x H x D	1.75 x 60 x 2.25 in. (45 x 1524 x 5845 mm)
Mounting	0U Vertical
Alternating Phase	No

## SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
STV-2001C	30	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 60 x 2.25 in. (58 x 1524 x 45 mm)	0U Vertical	No
C-12H1B211E7	12	2.8kW	120V	30A	1-Phase (L-N)	NEMA L5-30P	17.2 x 1.75 x 5 in. (437 x 45 x 127 mm)	1U Horizontal	No
C-12H2C211	12	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	17.2 x 1.75 x 5 in. (437 x 45 x 127 mm)	1U Horizontal	No

Not all part numbers are listed. Please contact a representative for a full portfolio of options.

Can't find the right PDU? Server Technology has you covered.



### RACK PDU SELECTOR

Quickly find your PDU

[servertech.com/product-selector](http://servertech.com/product-selector)

## BASIC PDUs



Basic Rack PDUs from Server Technology are UL Listed and meet IEC data center requirements. Optional flexible mounting and color identification features are available. Basic PDUs provide reliable power distribution for all devices in your equipment cabinet and range in power from 2kW-6kW per cabinet. Basic PDUs are available in single-phase 110-120V or 208-240V power distribution with 20A or 30A options and 3-phase power distribution with 20A and 30A options.

## POPULAR CONFIGURATIONS

### PRO3X MODEL: C3B36RL-GPJE0AT2 415V/400V 3 Phase Wye 30A/32A



Input Power Capacity	17.3kW/22kW
Input Voltage	415V/400V
Input Current	30/32A
Phase	3-Phase Wye (L-N)
Plug Type	230/400 32A & 240/415V Wye 30A IEC 60309 3P+N+G 6Hr
W x H x D	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)
Mounting	0U Vertical
Alternating Phase	No

### PRO1 MODEL: CB-26V2CE01F6 208V Single Phase 30A



Input Power Capacity	5kW
Input Voltage	208V
Input Current	30A
Phase	1-Phase (L-L)
Plug Type	NEMA L6-30P
W x H x D	1.75 x 35.5 x 1.75 in. (45 x 902 x 45 mm)
Mounting	0U Horizontal
Alternating Phase	No

## SAMPLE CONFIGURATIONS

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Input Plug Type	WxHxD	Mounting	Alt Phase
C3B36RL-2CJE0AT4	36*	5.0kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C3B36RL-EPJE0AT4	36*	7.3kW	230V	32A	1-Phase (L-N)	IEC 230V/32A 2P+PE 6Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C3B36RL-YCJE0AT3	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	1U Horizontal	No
C3B36RL-5CJE0AT2	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	1U Horizontal	No
C3B36RL-YQJE0AT2	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	208V Wye 60A IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	1U Horizontal	No
C3B36RL-DQJE0AT2	36*	17.3kW	208V	60A	3-Phase Delta (L-L)	208V Delta 60A IEC 60309 3P+G 9Hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
C3B36RL-GPJE0AT2	36*	17.3kW 22kW	415V 400V	30A 32A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6hr	2.2 x 70 x 2.5 in. (56 x 1778 x 64 mm)	0U Vertical	No
CB-26V2CE01F6	26	5.0kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 35.5 x 1.75 in. (45 x 902 x 45 mm)	0U Vertical	No
CB-12H1-C20	12	1.9kW	120V	20A	1-Phase (L-N)	IEC C20 Inlet	17 x 1.75 x 2.25 in. (58 x 45 x 432 mm)	1U Horizontal	No
CB-12H1-L530	12	2.8kW	120V	30A	1-Phase (L-N)	NEMA L5-30P	17.2 x 1.75 x 2.25 in. (58 x 45 x 437 mm)	1U Horizontal	No
CB-12H2-C20	12	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 Inlet	17 x 1.75 x 2.25 in. (58 x 45 x 432 mm)	1U Horizontal	No

\*Contains HDOT Cx Outlets

Not all part numbers are listed. Please contact a representative for a full portfolio of options.

Can't find the right PDU? Server Technology has you covered.



### RACK PDU SELECTOR

Quickly find your PDU

[servertech.com/product-selector](https://servertech.com/product-selector)



## -48VDC PDUs



-48VDC PDUs control cabinet equipment at remote locations, including colocation facilities and network ops centers, allowing you to reboot locked-up remote servers around the clock. Features include individual outlet current outputs, measurements, and automated alerts for several low and high current needs for the given environmental conditions.

-48VDC PDUs feature outputs individually protected by a fuse or breaker for over-current events. Low-current GMT fuses have a visual indicator that shows when they're blown. Because the fuses are rated as disconnect switches, they can be hot-swappable without removing power to input-feeds. Optional temperature and humidity probes with 10-ft cords to allow sensors to be located in different locations for complete environmental monitoring.

## POPULAR CONFIGURATIONS

### PRO2 MODEL: 48DCWC-16-2X600-E0

#### -48VDC 600A Dual-Input

Input Power Capacity	57.6kW
Input Voltage	-48V
Input Current	1200A
Phase	DC
Input Type	Terminals
W x H x D	17.0 x 7.0 x 32.0 in. (432 x 178 x 813 mm)
Mounting	4U Horizontal
Alternating Phase	No

### PRO2 MODEL: 48DCWC-04-2X100-D0NB

#### -48VDC 100A Dual-Input

Input Power Capacity	9.6kW
Input Voltage	-48V
Input Current	200A
Phase	DC
Input Type	Terminals
W x H x D	17.0 x 3.5 x 16.0 in. (432 x 89 x 407 mm)
Mounting	2U Horizontal
Alternating Phase	No

## SAMPLE CONFIGURATIONS

Model	Total Outputs	Input Power Capacity	Input Voltage	Input Current	Input Type	WxHxD	Mounting	Alt Phase
<b>PRO2 Models</b>								
48DCWC-04-2X100-D0NB	4	9.6kW	-48V	200A	Terminals	17 x 3.5 x 16 in. (432 x 89 x 407 mm)	2U Horizontal	No
48DCWC-08-2X100-B0NB	8	9.6kW	-48V	200A	Terminals	17 x 3.5 x 17.6 in. (432 x 89 x 447 mm)	2U Horizontal	No
48DCWC-12-2X100-A1NB	12	9.6kW	-48V	200A	Terminals	17 x 3.5 x 17.6 in. (432 x 89 x 447 mm)	2U Horizontal	No
48DCWC-16-2X100-A0	16	9.6kW	-48V	200A	Terminals	17 x 3.5 x 12 in. (432 x 89 x 305 mm)	2U Horizontal	No
48DCWC-04-4X070-D0NB	4	13.4kW	-48V	280A	Terminals	17 x 4.4 x 16 in. (432 x 112 x 407 mm)	2.5U Horizontal	No
48DCWC-04-4X125-E0NB	4	24kW	-48V	500A	Terminals	17 x 4.4 x 16 in. (432 x 112 x 407 mm)	2.5U Horizontal	No
48DCWC-10-2X300-E0NB	10	28.8kW	-48V	600A	Terminals	17 x 5.25 x 22 in. (432 x 134 x 559 mm)	3U Horizontal	No
48DCWC-16-2X600-E0	16	57.6kW	-48V	1200A	Terminals	17 x 7 x 32 in. (432 x 178 x 813 mm)	4U Horizontal	No

Not all part numbers are listed. Please contact a representative for a full portfolio of options.

**Can't find the right PDU? Server Technology has you covered.**









### RACK PDU SELECTOR

Quickly find your PDU






[servertech.com/product-selector](https://servertech.com/product-selector)

## POWER CORDS AND ACCESSORIES




### 20A PLUGS and CORDS

Model	PTCORD-L1	PTCORD-L5	PTCORD-L6	PTCORD-L7	HARD-WIRED	HARD-WIRED
Outlets	L6-20P to C19	5-15P to C19	5-20P to C19	L5-20P to C19	NEMA L15-20P	NEMA L21-20P
Voltage	208-240V	100-120V	100-120V	100-120V	3-Phase 208V, Delta	3-Phase 208V, Wye
Amps	20A	15A	20A	20A	20A	20A
Length	10'   3m	10'   3m	10'   3m	10'   3m	10'   3m	10'   3m
Profile						






### 30A PLUGS and CORDS

Model	HARD-WIRED	HARD-WIRED	HARD-WIRED	HARD-WIRED	HARD-WIRED
Outlets	NEMA L5-30P	NEMA L6-30P	NEMA L15-30P	NEMA L21-30P	NEMA L22-30P
Voltage	100-120V	208-240V	3-Phase 208V, Delta	3-Phase 208V, Wye	277/480V, Wye
Amps	30A	30A	30A	30A	30A
Length	10'   3m	10'   3m	10'   3m	10'   3m	10'   3m
Profile					

### 50A and 60A PLUGS and CORDS

Model	HARD-WIRED	HARD-WIRED	HARD-WIRED
Outlets	CS8365C	IEC 60309 (4pin, 9hr)	IEC 60309 (5pin, 9hr)
Voltage	3-Phase 208-240V, Delta	3-Phase 208-240V, Delta	3-Phase 208V, Wye
Amps	50A	60A	60A
Length	Varies Based on Model	Varies Based on Model	Varies Based on Model
Profile			

### ACCESSORY OPTIONS

Model	DX2 SmartSensors	EMTH-2-10	EMCU-1-1C	KIT-SUS-01	KIT-PRO2LINK-01D
Desc	Environmental Monitoring, Asset Location, Physical Access, and other Monitoring and Security Sensors.	Temperature & Humidity Probes	Environmental Monitoring Control Unit	StartUp Stick	Multi-Link Module
Product Series	PRO3X, PRO4X	PRO1, PRO2	PRO1, PRO2	PRO1, PRO2	PRO1, PRO2
Function	Available sensors for the PRO3X and PRO4X PDUs	Combination probe measures cabinet temperature & humidity	Supports additional 2 temp/humidity, 1 water & 4 dry contact closure door sensors	Easy solution to PDU configuration, start up in 5 seconds	Add up to 3 Expansion PDUs to one Master to share one IP address
Profile					

Not all part numbers are listed. Please contact a representative for a full portfolio of options.

## LEGRAND UNIVERSAL INPUT CORDS (UIC)

Part numbers are compatible with the PRO4X Rack PDU's Universal Input. This unique PRO4X solution allows you to purchase a single PDU and, as needed, swap the input cord to match the power infeed requirements.

Part Number	Plug Type	Rating	kVA / kW	Region
<b>Single Phase Cord Options</b>				
DTCORD-L630	NEMA L6-30P	200-240V / 24A	4.8 - 5.8	North America
DTCORD-1P32	IEC60309 32A	200-240V / 32A	6.4 - 7.7	Europe
DTCORD-1P3G*	IEC60309 30/32A	200-240V / 24A	4.8 - 5.8	Global
	IEC60309 30/32A	200-240V / 32A	6.4 - 7.7	Global
DTCORD-1P60	IEC60309 60A	200-240V / 48A	9.6 - 11.5	North America
<b>3-Phase Delta Cord Options</b>				
DTCORD-L1530	NEMA L15-30P Delta	208-240V / 24A	8.6 - 10	North America
DTCORD-CS836	CS8365C Delta	208-240V / 40A	14.4 - 16.6	North America
DTCORD-3P60	IEC60309 60A 3P Delta	208-240V / 48A	17.3 - 20	North America
<b>3-Phase Wye Cord Options</b>				
DTCORD-L213D	NEMA L21-30P Wye	190-208V / 24A	7.9 - 8.6	North America
DTCORD-L2230	NEMA L22-30P Wye	346-415V / 24A	14.4 - 17.3	North America
DTCORD-3P32	IEC60309 32A 3PY Wye	346-415V / 32A	19.2 - 23	Europe
DTCORD-3P3G*	IEC60309 30/32A 3PY Wye	346-415V / 24A	14.4 - 17.3	Global
	IEC60309 30/32A 3PY Wye	346-415V / 32A	19.2 - 23	Global

Resulting PDU capacity determined by its nominal ratings and number of internal circuit breakers. Refer to PDU specifications for more information.


Standard 3m cord length.

\*Denotes a dual-rated cord.




# RACK PDU SELECTOR


Browse hundreds of PDU configurations at [servertech.com/product-selector](http://servertech.com/product-selector)



The Rack PDU Selector allows you to filter type, mounting, outlets, voltage, current, phase and plug type.



The product family page will show you specifications and features for that product family.



Click Contact Us or Buy Now and an authorized representative will contact you.

To learn more visit  
**servertech.com**

©2025 Legrand. All rights reserved. The industry-leading brands of Approved Networks, Ortronics, Raritan, Server Technology, and Starline empower Legrand's Data, Power & Control to produce innovative solutions for data centers, building networks, and facility infrastructures. Our division designs, manufactures, and markets world-class products for a more productive and sustainable future. The exceptional reliability of our technologies results from decades of proven performance and a dedication to research and development. LIT# V1996

**Server Technology, Inc**  
800.835.1515  
servertech.com

**Server  
Technology**  
A brand of  **legrand**