




SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

| REVISION HISTORY | | | | |
|------------------|-----|----------------|-----------|----------|
| ZONE | REV | DESCRIPTION | DATE | APPROVED |
| - | 1 | INITIAL DESIGN | 12/2/2014 | JWM/ROG |



| Part Number | Expansion | Certification | Input | Output | | | |
|------------------------------|------------------------------|---------------------|--------------------------------|--------------|-------------------------|--|-------------------------|
| Master | Expansion | Rating Standard | Rating | Input Type | Total Output Rating | Outlet Type and Ratings | Branch Circuit Rating |
| C2W30VY-DBLE2SE2 (STV-4502D) | C2X30VY-DBLE2SE2 (SEV-4502D) | cTUVus and/or cULus | 208V 3P+PE, 50/60Hz; 16A | NEMA L15-20P | 208V, 50/60Hz; <= 27.7A | IEC 60320: 6xC19 <= 16A each, 24xC13 <= 12A each | 3 branches, each <= 16A |
| C2W30VY-DCLE2SE2 (STV-4502E) | C2X30VY-DCLE2SE2 (SEV-4502E) | cTUVus and/or cULus | 208V 3P+PE, 50/60Hz; 24A | NEMA L15-30P | 208V, 50/60Hz; <= 41.5A | IEC 60320: 6xC19 <= 16A each, 24xC13 <= 12A each | 3 branches, each <= 16A |
| C2W30VY-YBLE2SE2 (STV-4502L) | C2X30VY-YBLE2SE2 (SEV-4502L) | cTUVus and/or cULus | 120/208V 3P+N+PE, 50/60Hz; 16A | NEMA L21-20P | 208V, 50/60Hz; <= 27.7A | IEC 60320: 6xC19 <= 16A each, 24xC13 <= 12A each | 3 branches, each <= 16A |
| C2W30VY-YCLE2SE2 (STV-4502M) | C2X30VY-YCLE2SE2 (SEV-4502M) | cTUVus and/or cULus | 120/208V 3P+N+PE, 50/60Hz; 24A | NEMA L21-30P | 208V, 50/60Hz; <= 41.5A | IEC 60320: 6xC19 <= 16A each, 24xC13 <= 12A each | 3 branches, each <= 16A |



DETAIL A
 C2X EXPANSION

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .130

ANGULAR DIMENSIONS:
 X = ± 1°
 XX = ± .5°
 XXX = ± .25°

SYMBOLS
 (Q#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

MATERIAL:
 FINISH:

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL BLOCK WIRING DIAGRAM,
 CDU2, SWITCHED, PIPS**

| | | | |
|-------------|-----------|-------------|--------|
| SIZE | CAGE CODE | DWG NO. | REV |
| B | 049V0 | 495-0761-20 | 1 |
| SCALE: NONE | SHEET | | 1 OF 1 |