




RoHS COMPLIANT

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	7/9/2015	JWM/ROG


NOTES:

- SEE STI QUALITY STANDARD #104-1000-1 FOR GENERAL REQUIREMENTS.



ISO VIEW

Part Number	Expansion	Certification	Input	Output	Branch Circuit Rating		
Model	Expansion	Rating Standard	Rating	Input Type	Output Rating North America	Outlet Type and Ratings	Branch Circuit Rating
CS-24VD-L20MA	CL-24VD-L20MA	cTUVus and/or cULus	240V 3W+PE, 50/60Hz; 16A	NEMA L15-20P	240V, 50/60Hz; <= 27.6A	IEC 60320: C13 <= 12A each C19 <=16A each	3 branches, each <= 16A
CS-24VDD313A1	CL-24VDD313A1	cTUVus and/or cULus	240V 3W+PE, 50/60Hz; 16A	NEMA L15-20P	240V, 50/60Hz; <= 27.6A	IEC 60320: C13 <= 12A each	3 branches, each <= 16A
CS-24VD-L30MA	CL-24VD-L30MA	cTUVus and/or cULus	240V 3W+PE, 50/60Hz; 24A	NEMA L15-30P	240V, 50/60Hz; <= 41.6A	IEC 60320: C13 <= 12A each C19 <=16A each	3 branches, each <= 16A
CS-24VDE313A1	CL-24VDE313A1	cTUVus and/or cULus	240V 3W+PE, 50/60Hz; 24A	NEMA L15-30P	240V, 50/60Hz; <= 41.6A	IEC 60320: C13 <= 12A each	3 branches, each <= 16A
CS-24VY-L20MA	CL-24VY-L20MA	cTUVus and/or cULus	120/208V 3W+N+PE, 50/60H	NEMA L21-20P	208V, 50/60Hz; <= 27.6A	IEC 60320: C13 <= 12A each C19 <=16A each	3 branches, each <= 16A
CS-24VYL313A1	CL-24VYL313A1	cTUVus and/or cULus	120/208V 3W+N+PE, 50/60H	NEMA L21-20P	208V, 50/60Hz; <= 27.6A	IEC 60320: C13 <= 12A each	3 branches, each <= 16A
CS-24VY-L30MA	CL-24VY-L30MA	cTUVus and/or cULus	120/208V 3W+N+PE, 50/60H	NEMA L21-30P	208V, 50/60Hz; <= 41.6A	IEC 60320: C13 <= 12A each C19 <=16A each	3 branches, each <= 16A
CS-24VYL313A1	CL-24VYL313A1	cTUVus and/or cULus	120/208V 3W+N+PE, 50/60H	NEMA L21-30P	208V, 50/60Hz; <= 41.6A	IEC 60320: C13 <= 12A each	3 branches, each <= 16A
CS-24VAV311A1	CL-24VAV311A1	cTUVus and/or cULus	240V 3W+PE, 50/60Hz; 35A	CS8365 50A	208V, 50/60Hz; <= 60A	IEC 60320: C13 <= 12A each C19 <=16A each	3 branches, each <= 20A
CS-24VAV313A1	CL-24VAV313A1	cTUVus and/or cULus	240V 3W+PE, 50/60Hz; 35A	CS8365 50A	208V, 50/60Hz; <= 60A	IEC 60320: C13 <= 12A each	3 branches, each <= 20A



DETAIL A
 'CL' EXPANSION VIEW

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .130

ANGULAR DIMENSIONS:
 X = ± 1°
 X.X = ± .5°
 X.XX = ± .25°

SYMBOLS
 (Q#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

MATERIAL:
 FINISH:

SERVER TECHNOLOGY, INC.
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL BLOCK WIRING DIAGRAM,
 SMART**

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0350-36	1
SCALE: NONE	SHEET 1 OF 1		