




SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	02/27/2013	JSL/VB



Part Number	Expansion	Input	Output
Master	Expansion	Rating, North America	Input Type
CSG-24VYL425C9	CLG-24VYL425C9	120/208V 3W+N+PE, 50/60Hz; 16A	NEMA L21-20P
CSG-24VYM425C9	CLG-24VYM425C9	120/208V 3W+N+PE, 50/60Hz; 24A	NEMA L21-30P

TOLERANCES (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .130


ANGULAR DIMENSIONS:
 X = ± 1°
 X.X = ± .5°
 X.XX = ± .25°

SYMBOLS
 (Q#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

MATERIAL:
 FINISH:

SERVER TECHNOLOGY, INC. 

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL BLOCK WIRING DIAGRAM,
 SMART POPS V24**




SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0743-2	1
SCALE: NONE			SHEET 1 OF 2

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT



ISO VIEW

Part Number	Expansion	Input	Output					
Master	Expansion	Rating, North America	Input Type	Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CSG-24VDD425A1	CLG-24VDD425A1	240V 3W+PE, 50/60Hz; 16A	NEMA L15-20P	240V, 50/60Hz; <= 27.6A	6x C19 <= 9.2A, 18x C13 <= 9.2A	IEC 60320 C13 and C19	XY, YZ, XZ <= 9.2A	XY, YZ, XZ <= 9.2A
CSG-24VDE425A1	CLG-24VDE425A1	240V 3W+PE, 50/60Hz; 24A	NEMA L15-30P	240V, 50/60Hz; <= 41.6A	6x C19 <= 13.9A, 18x C13 <= 12A	IEC 60320 C13 and C19	XY, YZ, XZ <= 13.9A	XY, YZ, XZ <= 13.9A

<p>TOLERANCES (UNLESS OTHERWISE SPECIFIED)</p> <p>LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130</p> <p>ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25°</p> <p>SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE</p>	<p>UNLESS OTHERWISE SPECIFIED</p> <p>* INTERPRET DRAWING IAW ASME Y14.100-2000</p> <p>* DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007</p> <p>* REMOVE ALL BURRS AND SHARP EDGES .2 R MAX</p> <p>* DIMENSIONS ARE IN MILLIMETERS</p> <p>* DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.</p> <p>DO NOT SCALE DRAWING</p> <p>THIRD ANGLE PROJECTION</p>	<p>SERVER TECHNOLOGY, INC.</p> <p>1040 Sandhill Drive Reno, NV 89521</p> <p>DRAWING TITLE: FUNCTIONAL BLOCK WIRING DIAGRAM, SMART POPS V24</p>			
		<p>MATERIAL:</p> <p>FINISH:</p>	<p>SIZE: B</p> <p>CAGE CODE: 049V0</p> <p>DWG NO.: 495-0743-2</p> <p>SCALE: NONE</p>	<p>REV: 1</p> <p>SHEET: 2 OF 2</p>	