



Part Number	Expansion	Input		Input Type	Output		Outlet: North America / PSE	Outlet Type	Branch Circuit: North America / PSE
		Rating, North America	PSE Japan		Output Rating North America	PSE Japan			
CW-16H1A454	CX-16H1A454	100-120V, 50/60Hz; 16A	100-120V, 50/60Hz; 20A	IEC 60320 C20 Inlet	100-120V, 50/60Hz; <= 16A	100-120V, 50/60Hz; <= 20A	<= 16A / <= 17A	NEMA 5-20R	<= 16A / <= 20A
CW-16H1B454	CX-16H1B454	100-120V, 50/60Hz; 24A	100-120V, 50/60Hz; <= 30A	NEMA L5-30P	100-120V, 50/60Hz; <= 24A	100-120V, 50/60Hz; <= 30A	<= 16A / <= 17A	NEMA 5-20R	<= 16A / <= 20A

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .130

ANGULAR DIMENSIONS:
 X = ± 1°
 X.X = ± .5°
 X.XX = ± .25°

SYMBOLS
 (Q#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

MATERIAL:
 FINISH:

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL WIRING DIAGRAM,
 SWITCHED PIPS H16 120V**

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0651-1	1
SCALE: NONE			SHEET 1 OF 1