


SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	6/30/2014	JWM/ROG
-	1A	ADDED C19 OUTLET RATING	7/1/2014	JWM/ROG



Part Number	Rating Standard	Input		Output					
		Rating	Input Type	Total Output Rating	Outlet Type 1	Outlet Rating 1	Outlet Type 2	Outlet Rating 2	Branch Circuit Rating
CB-26V2CE01F6	cTUVus	208-240V, 50/60Hz; 24A	NEMA L6-30P	208-240V, 50/60Hz; <= 24A	IEC 60320 C13	<= 12A	IEC 60320 C19	<= 16A	<= 16A
CB-26VEKE01F6	TUV-GS	230V, 50/60Hz; 32A	IEC 60309 32A	230V, 50/60Hz; <= 32A	IEC 60320 C13	<= 10A	IEC 60320 C19	<= 16A	<= 16A

ISO VIEW

<p>TOLERANCES (UNLESS OTHERWISE SPECIFIED)</p> <p>LINEAR DIMENSIONS: X = ± .500 XX = ± .300 .XXX = ± .130</p> <p>ANGULAR DIMENSIONS: X = ± 1° XX = ± .5° XXX = ± .25°</p> <p>SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE</p>	<p>UNLESS OTHERWISE SPECIFIED</p> <p>* INTERPRET DRAWING IAW ASME Y14.100-2000</p> <p>* DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007</p> <p>* REMOVE ALL BURRS AND SHARP EDGES .2 R MAX</p> <p>* DIMENSIONS ARE IN MILLIMETERS</p> <p>* DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.</p> <p>DO NOT SCALE DRAWING</p> <p>THIRD ANGLE PROJECTION</p>	<p>SERVER TECHNOLOGY, INC.</p> <p>1040 Sandhill Drive Reno, NV 89521</p>	
		<p>DRAWING TITLE: FUNTIONAL BLOCK WIRING DIAGRAM, V26 BASIC</p>	
		<p>SIZE: B</p>	<p>CAGE CODE: 049V0</p>
<p>SCALE: NONE</p>		<p>SHEET 1 OF 1</p>	