



8 7 6 5 4 3 2 1

SERVER TECHNOLOGY, INC.  
**PROPRIETARY INFORMATION**  
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.  
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	6/15/11	MB/PG
1A	CORRECTED TOROID LOCATION	5/21/12	JSL/TI

NOTES:



Part Number		Input		Output				
Model		Rating, North America	Input Type	Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CS-12HDDD454A3	CL-12HDDD454A3	240V 3W+PE, 50/60Hz; 2x 16A	NEMA L15-20P	240V, 50/60Hz; A, B <= 27.6A	<= 9.2A	IEC 60320 C19	XY, YZ, XZ <= 9.2A	XY, YZ, XZ <= 9.2A
CS-12HDDE454A3	CL-12HDDE454A3	240V 3W+PE, 50/60Hz; 2x 24A	NEMA L15-30P	240V, 50/60Hz; A, B <= 41.6A	<= 12A	IEC 60320 C19	XY, YZ, XZ <= 13.9A	XY, YZ, XZ <= 13.9A
CS-12HDYL454A3	CL-12HDYL454A3	120/208V 3W+N+PE, 50/60Hz; 2x 16A	NEMA L21-20P	208V, 50/60Hz; A, B <= 27.6A	<= 9.2A	IEC 60320 C19	XY, YZ, XZ <= 9.2A	XY, YZ, XZ <= 9.2A
CS-12HDYM454A3	CL-12HDYM454A3	120/208V 3W+N+PE, 50/60Hz; 2x 24A	NEMA L21-30P	208V, 50/60Hz; A, B <= 41.6A	<= 12A	IEC 60320 C19	XY, YZ, XZ <= 13.9A	XY, YZ, XZ <= 13.9A

<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .150 ANGULAR DIMENSIONS: X.X = ± 5° X.XX = ± .25°	<b>UNLESS OTHERWISE SPECIFIED</b> * INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.100-2000 DIMENSIONING & TOLERANCING IN ACCORDANCE WITH ASME Y14.5M-1994 REMOVE ALL BURRS AND SHARP EDGES 2 R MAX DIMENSIONS ARE IN MILLIMETERS DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING <b>DO NOT SCALE DRAWING</b>	<b>SERVER TECHNOLOGY, INC.</b> 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: <b>FUNCTIONAL WIRING DIAGRAM</b> ENA-0520-2G
<b>SYMBOLS</b> (Q.S.) = CRITICAL DIM. (C) = COSMETIC SURFACE	<b>THIRD ANGLE PROJECTION</b> 	
<b>MATERIAL:</b> <b>FINISH:</b>		SIZE: B CAGE CODE: 04V90 DWG NO.: 495-0603-2 REV: 1A SCALE: 1/1 SHEET: 1 OF 1

8 7 6 5 4 3 2 1