

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION





THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	4/26/13	AJS/TI

- NOTES:
- DIMENSIONS ARE IN MILLIMETERS AND [] ARE IN INCHES.
 - DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.



DETAIL B
 EXPANSION UNIT


TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25°	UNLESS OTHERWISE SPECIFIED • INTERPRET DRAWING IAW ASME Y14.100-2000 • DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 • REMOVE ALL BURRS AND SHARP EDGES .2 R MAX • DIMENSIONS ARE IN MILLIMETERS • DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.
	DO NOT SCALE DRAWING THIRD ANGLE PROJECTION
SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	MATERIAL: FINISH:

SERVER TECHNOLOGY, INC.


1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**OUTLINE DRAWING, SWITCHED, PIPS
 POPS, V30**


SIZE	CAGE CODE	DWG NO.	REV
B	049V0	412-0536-41	1
SCALE: NONE			SHEET 1 OF 3




MOUNTING BRACKET POSITIONING OPTIONS




OPTION A - MB-0005-IPT7




OPTION B - MB-0005-IPT7



OPTION C - MB-0005-IPT7



OPTION D - MB-0005-IPT7



***DETAIL A**

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25°	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.
	DO NOT SCALE DRAWING THIRD ANGLE PROJECTION
SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	MATERIAL: FINISH:

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
OUTLINE DRAWING, SWITCHED, PIPS POPS, V30

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	412-0536-41	1
SCALE: NONE			SHEET 2 OF 3

8 7 6 5 4 3 2 1



SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION


THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	4/26/13	AJS/TI



TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25°		UNLESS OTHERWISE SPECIFIED • INTERPRET DRAWING IAW ASME Y14.100-2000 • DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 • REMOVE ALL BURRS AND SHARP EDGES .2 R MAX • DIMENSIONS ARE IN MILLIMETERS • DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING THIRD ANGLE PROJECTION 		SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: OUTLINE DRAWING, SWITCHED, PIPS POPS, V30	
SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE		MATERIAL: FINISH:		SIZE: B CAGE CODE: 049V0 DWG NO.: 412-0536-41 REV: 1	
		SCALE: NONE		SHEET 3 OF 3	

8 7 6 5 4 3 2 1