

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION


THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT


REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	6/16/2016	

Vertical PDU Input Power Cord Top or Bottom Entry



L = Input power cord length (Typically 3.05 m / 10 ft unless otherwise specified by part number or description)

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: X = ± .500 XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25°	UNLESS OTHERWISE SPECIFIED • INTERPRET DRAWING IAW ASME Y14.100-2000 • DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 • REMOVE ALL BURRS AND SHARP EDGES .2 R MAX • DIMENSIONS ARE IN MILLIMETERS • DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING THIRD ANGLE PROJECTION
SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	MATERIAL: FINISH:

SERVER TECHNOLOGY, INC. 

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
PDU Input Power Cord Length Measurement

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	412-Powercord	1
SCALE: NONE		SHEET 1 OF 3	

8 7 6 5 4 3 2 1


SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

Vertical PDU Input Power Cord Front Face Entry



FRONT FACE VIEW NEMA IEC 60309 HARTING CLIPSAL CS8365

L = Input power cord length (Typically 3.05 m / 10 ft unless otherwise specified by part number or description)

SERVER TECHNOLOGY, INC. 

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**PDU Input Power Cord Length
 Measurement**







SIZE	CAGE CODE	DWG NO.	REV
B	049V0	412-Powercord	1
SCALE: NONE		SHEET 2 OF 3	

8 7 6 5 4 3 2 1


RoHS COMPLIANT

SERVER TECHNOLOGY, INC
PROPRIETARY INFORMATION
THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

Horizontal PDU Input Power Cord Entry



L = Input power cord length (Typically 3.05 m / 10 ft unless otherwise specified by part number or description)

SERVER TECHNOLOGY, INC. 

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
PDU Input Power Cord Length Measurement

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	412-Powercord	1
SCALE: NONE		SHEET 3 OF 3	