

Network Port Requirements for SPM

SUPPORT NOTE SN-3001 | May 2015

Overview

This Note provides guidance for port usage of SPM over a TCP/IP network.

Table

Port	Service
20/21	FTP data transfer / control
22	SSH/SFTP
23	Telnet
25	SMTP
49	TACACS+
67/68	DHCP
80	HTTP
123	NTP
161/162	SNMP
443	SSL / SPM SNAP
514	SYSLOG
389	LDAP
636	LDAPS
3268	Microsoft Global Catalogue
3269	Microsoft Global Catalogue over SSL

- SNMP is primary communication from SPM to CDUs.
 - This must be open.
- SSL connection port for HTTPS browser access to SPM can be changed; however, port 443 must remain open for SPM SNAP communication to CDUs.
- All other ports are for optional access

For additional assistance with Server Technology products visit us online at: www.servertech.com/support



Server Technology
Quality Rack Power Solutions



Stay Powered



Be Supported



Get Ahead

From Your Power Strategy Experts

HEADQUARTERS NORTH AMERICA

Server Technology
1040 Sandhill Drive
Reno, NV 89521
United States
Tel: +1.775.284.2000
Fax: +1.775.284.2065
sales@servertech.com
www.servertech.com
www.servertechblog.com

WESTERN EUROPE, MIDDLE EAST & AFRICA

Server Technology
Fountain Court
2 Victoria Square
Victoria Street
St. Albans, AL1 3TF
United Kingdom
Tel: +44 (0) 1727 884676
Fax: +44 (0) 1727 220815
salesint@servertech.com

CENTRAL EUROPE, EASTERN EUROPE & RUSSIA NIEDERLASSUNG DEUTSCHLAND

Server Technology
42119 Wuppertal
Germany
Tel: +49 202 693917 x0
Fax: +49 202 693917-10
salesint@servertech.com

APAC

Server Technology
Room 2301, 23/F, Future Plaza
111-113 How Ming Street,
Kwun Tong, Hong Kong
Tel: +852 3916 2048
Fax: +852 3916 2002
salesint@servertech.com