



NOTES:

1. DIMENSIONS ARE IN MILLIMETERS AND [] BRACKETS ARE IN INCHES.
2. DIMENSIONS ARE NOMINAL. INFORMATION IS SUBJECT TO CHANGE WITHOUT NOTICE.



DETAIL A
OPTIONAL OUTLETS CONFIGURATIONS

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25°	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING THIRD ANGLE PROJECTION 	SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521												
SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	MATERIAL: FINISH:	DRAWING TITLE: OUTLINE DRAWING, SMART/SWITCHED, PIPS, V48/54												
		<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width: 15%;">SIZE</td> <td style="width: 20%;">CAGE CODE</td> <td style="width: 40%;">DWG NO.</td> <td style="width: 25%;">REV</td> </tr> <tr> <td style="text-align: center;">B</td> <td style="text-align: center;">049V0</td> <td style="text-align: center;">412-1083-32</td> <td style="text-align: center;">1</td> </tr> <tr> <td colspan="2">SCALE: NONE</td> <td colspan="2">SHEET 1 OF 1</td> </tr> </table>	SIZE	CAGE CODE	DWG NO.	REV	B	049V0	412-1083-32	1	SCALE: NONE		SHEET 1 OF 1	
SIZE	CAGE CODE	DWG NO.	REV											
B	049V0	412-1083-32	1											
SCALE: NONE		SHEET 1 OF 1												