

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION






THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	10/13/2016	JWM/ROG

- NOTES:
1. DIMENSIONS ARE IN MILLIMETERS AND [] ARE IN INCHES.
 2. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.



DETAIL A
48DCW MASTER OPTION



DETAIL B
48DCX LINK OPTION

<p>TOLERANCES (UNLESS OTHERWISE SPECIFIED)</p> <p>LINEAR DIMENSIONS: X = ± .5 .XX = ± .30 .XXX = ± .130</p> <p>ANGULAR DIMENSIONS: X = ± 1° XX = ± .5° XXX = ± .25°</p> <p>SYMBOLS (Q#) = CRITICAL DIM. (#) = COSMETIC SURFACE</p>	<p>UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2009 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER FINISH</p> <p>DO NOT SCALE DRAWING THIRD ANGLE PROJECTION</p>	<p>SERVER TECHNOLOGY, INC.</p> <p>1040 Sandhill Road, Reno, NV 89521</p>		
	<p>MATERIAL:</p> <p>FINISH:</p>	<p>DRAWING TITLE: OUTLINE DRAWING 48DC[W/X]B MODELS WITH MOUNTING BRACKET OPTIONS</p>		
<p>SIZE: B</p>		<p>CAGE CODE: 049V0</p>	<p>DWG NO.: 412-4870-25</p>	<p>REV: 1</p>
<p>SCALE: NONE</p>		<p>SHEET 1 OF 1</p>		