

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION



THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	03/04/2015	JM/VB
-	A	UPDATED SIDE VIEW TO REFLECT ADDITIONAL 4X M3 FLATHEAD SCREWS	7/27/2015	JM/VB
	A1	ADD 21XC13 MODULE	12/22/2015	JM/ROG


- NOTES:
- DIMENSIONS ARE IN MILLIMETERS AND [ ] BRACKETS ARE IN INCHES.
  - DIMENSIONS ARE NOMINAL. INFORMATION IS SUBJECT TO CHANGE WITHOUT NOTICE.



SEE DETAIL A FOR ALL OUTLET CONFIGURATIONS




(21)C13




(18)C13



(6)C19, (12)C13



(3)C19, (15)C13



(9)C19, (9)C13

DETAIL A  
 OPTIONAL OUTLET CONFIGURATIONS

<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) <b>LINEAR DIMENSIONS:</b> .X = ± .500 .XX = ± .300 .XXX = ± .130  <b>ANGULAR DIMENSIONS:</b> X = ± 1° X.X = ± .5° X.XX = ± .25°	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.
	DO NOT SCALE DRAWING THIRD ANGLE PROJECTION 
<b>SYMBOLS</b> (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	<b>MATERIAL:</b>  <b>FINISH:</b>

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:  
**OUTLINE DRAWING, SMART/SWITCHED, PIPS, V36/42**

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	412-0983-32	A1
SCALE: NONE			SHEET 1 OF 1

8

7

6

5

4

3

2

1

SERVER TECHNOLOGY, INC  
PROPRIETARY INFORMATION

RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	6/7/2016	JM/VB


NOTES:

- SEE STI QUALITY STANDARD #104-1000-1 FOR GENERAL REQUIREMENTS.
- THE INFORMATION PROVIDED IS SUBJECT TO CHANGE WITHOUT NOTICE.


**SMART/SWITCHED VERSIONS**




**(18)C13**



**(21)C13**



**(3)C19, (15)C13**




**(6)C19, (12)C13**



**(9)C19, (9)C13**


**SMART POPS/SWITCHED POPS VERSIONS**



**(18)C13**



**(3)C19, (15)C13**



**(6)C19, (12)C13**

**TOLERANCES**  
(UNLESS OTHERWISE SPECIFIED)

**LINEAR DIMENSIONS:**  
X = ± .5  
XX = ± .30  
XXX = ± .130

**ANGULAR DIMENSIONS:**  
X = ± 1°  
XX = ± .5°  
XXX = ± .25°

**SYMBOLS**

(G#) = CRITICAL DIM.  
(P) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED  
\* INTERPRET DRAWING IAW ASME Y14.100-2000  
\* DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2009  
\* REMOVE ALL BURRS AND SHARP EDGES 2 R MAX  
\* DIMENSIONS ARE IN MILLIMETERS  
\* DIMENSIONAL LIMITS APPLY AFTER FINISH

DO NOT SCALE DRAWING  
THIRD ANGLE PROJECTION

**MATERIAL:**

**FINISH:**

**SERVER TECHNOLOGY, INC.**

1040 Sandhill Road, Reno, NV 89521

DRAWING TITLE:  
**OUTLINE DRAWING, SMART/SWITCHED, POPS, HDOT MODULES, ENA-0983-XXH**

SIZE <b>B</b>	CAGE CODE <b>049V0</b>	DWG NO. <b>412-CMA-0983</b>	REV <b>1</b>
SCALE <b>NONE</b>		SHEET <b>1 OF 1</b>	

8

7

6

5

4

3

2

1