


SERVER TECHNOLOGY, INC  
**PROPRIETARY INFORMATION**

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	6/27/2016	JLT/ROG



Part Number	Certification	Input	Output
Master	Rating Standard	Rating	Total Output Rating
Expansion		Input Type	Outlet Type and Ratings
C1S24CB-4QAE27xx	TUVGS	230/400V 3P+N+PE, 50/60Hz; 63A	230V, 50/60Hz; <= 189A
C1L24CB-4QAE27xx			IEC 60320: C19 <= 16A each, C13 <= 10A each
			Branch Circuit Rating
			12 branches, each <= 16A



**TOLERANCES**  
 (UNLESS OTHERWISE SPECIFIED)  
 LINEAR DIMENSIONS:  
 .X = ± .5  
 .XX = ± .30  
 .XXX = ± .130  
 ANGULAR DIMENSIONS:  
 X = ± 1°  
 XX = ± .5°  
 XXX = ± .25°

**SYMBOLS**  
 (Q#) = CRITICAL DIM.  
 (#) = COSMETIC SURFACE

**UNLESS OTHERWISE SPECIFIED**  
 \* INTERPRET DRAWING IAW ASME Y14.100-2000  
 \* DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2009  
 \* REMOVE ALL BURRS AND SHARP EDGES .2 R MAX  
 \* DIMENSIONS ARE IN MILLIMETERS  
 \* DIMENSIONAL LIMITS APPLY AFTER FINISH

**DO NOT SCALE DRAWING**  
 THIRD ANGLE PROJECTION

**MATERIAL:**  
**FINISH:**

**SERVER TECHNOLOGY, INC.**

1040 Sandhill Road, Reno, NV 89521

DRAWING TITLE:  
**FUNCTIONAL BLOCK DRAWING, SMART, PIPS**

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-1010-6	1
SCALE: NONE	SHEET		1 OF 1