

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION



THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	9/22/11	MB/PG

NOTES:



Part Number		Input		Output		Outlet: North America / GS		Outlet Type	Branch Circuit: North America / GS
Master	Expansion	Rating, North America	GS	Input Type	Output Rating North America	GS			
CS-12HD2G454A3	CL-12HD2G454A3	208-240V, 50/60Hz; 2x 16A		NEMAL6-20P	208-240V, 50/60Hz; A, B <= 16A		<= 16A /	IEC 60320 C19	<= 16A /
CS-12HD2C454A3	CL-12HD2C454A3	208-240V, 50/60Hz; 2x24A		NEMAL6-30P	208-240V, 50/60Hz; A, B <= 24A		<= 16A /	IEC 60320 C19	<= 16A /
CS-12HDEJ454A3	CL-12HDEJ454A3		230V, 50/60Hz; 2x 16A	IEC 60320 C20 Inlet		230V, 50/60Hz; A, B <= 16A	/ <= 16A	IEC 60320 C19	/ <= 16A
CS-12HDEK454A3	CL-12HDEK454A3		230V, 50/60Hz; 2x 32A	IEC 60309 32A		230V, 50/60Hz; A, B <= 32A	/ <= 16A	IEC 60320 C19	/ <= 16A

SERVER TECHNOLOGY, INC. 
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL BLOCK WIRING DIAGRAM
 SMART, PIPS, H12**

SIZE B	CAGE CODE 049V0	DWG NO. 495-0603-1	REV 1
SCALE: 1/1		SHEET 1 OF 1	