


SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	10/31/2014	JWM/ROG



Part Number		Input				Output				
Master	Expansion	Rating: North America	GS	PSE	Input Type	Output Rating: North America	GS	PSE	Outlet: North America / GS / PSE	Outlet Type
CW-8H2A413	CX-8H2A413	200-240V, 50/60Hz; 16A		200V, 50/60Hz; 20A	IEC 60320 C20 Inlet	200-240V, 50/60Hz; <= 16A		200V, 50/60Hz; <= 20A	<= 12A // <= 15A	IEC 60320 C13
CW-8H2C413	CX-8H2C413	200-240V, 50/60Hz; 16A		200V, 50/60Hz; 20A	NEMA L6-30P	200-240V, 50/60Hz; <= 24A		200V, 50/60Hz; <= 30A	<= 12A // <= 15A	IEC 60320 C13
CW-8HEA413	CX-8HEA413		230V, 50/60Hz; 16A		IEC 60320 C20 Inlet		230V, 50/60Hz; <= 16A	/ <= 10A /		IEC 60320 C13
CW-8HEK413	CX-8HEK413		230V, 50/60Hz; 32A		IEC 60309 32A		230V, 50/60Hz; <= 32A	/ <= 10A /		IEC 60320 C13



DETAIL A
 CX EXPANSION

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .130

ANGULAR DIMENSIONS:
 X = ± 1°
 XX = ± .5°
 XXX = ± .25°

SYMBOLS
 (Q#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

MATERIAL:
 FINISH:

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL BLOCK DIAGRAM,
 SWITCHED, PIPS**

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0783-2	1
SCALE: NONE			SHEET 1 OF 1