

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.




THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	1/23/2017	JWM/ROG

NOTES:


1. SEE STI QUALITY STANDARD #104-1000-1 FOR GENERAL REQUIREMENTS.



ISO VIEW

Part Number	Expansion	Certification	Input	Output	Branch Circuit Rating		
Master	Expansion	Rating Standard	Rating	Input Type	Total Output Rating	Outlet Type and Ratings	Branch Circuit Rating
C2WxxCE-2CMFA9yy	C2XxxCE-2CMEA9yy	cTUVus and/or cULus	208V 2P+PE, 50/60Hz; 24A	NEMA L6-30P	208V, 50/60Hz; <= 24A	IEC 60320: C19 <= 16A each, C13 <= 12A each	3 branches, each <= 16A
C2WxxCE-2PMFA9yy	C2XxxCE-2PMEA9yy	cTUVus and/or cULus	230V 2P+PE, 50/60Hz; 32A	IEC 60309 32A	208V, 50/60Hz; <= 32A	IEC 60320: C19 <= 16A each, C13 <= 12A each	3 branches, each <= 16A
C2WxxCE-2HMFA9yy	C2XxxCE-2HMEA9yy	cTUVus and/or cULus	208V 2P+PE, 50/60Hz; 40A	CS8265 50A	208V, 50/60Hz; <= 40A	IEC 60320: C19 <= 16A each, C13 <= 12A each	3 branches, each <= 16A
C2WxxCE-2QMFA9yy	C2XxxCE-2QMEA9yy	cTUVus and/or cULus	208V 2P+PE, 50/60Hz; 48A	IEC 60309 60A	208V, 50/60Hz; <= 48A	IEC 60320: C19 <= 16A each, C13 <= 12A each	3 branches, each <= 16A

Note: "xx" designates total number of outlets and "yy" designates code for number of C19 outlets in each of the two outlet modules



DETAIL A
 'C2X' EXPANSION VIEW

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .5
 .XX = ± .30
 .XXX = ± .130

ANGULAR DIMENSIONS:
 X = ± 1°
 X.X = ± .5°
 X.XX = ± .25°

SYMBOLS
 (Q#) = CRITICAL DIM.
 (#) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2009
 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER FINISH

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

MATERIAL:
 FINISH:

SERVER TECHNOLOGY, INC.
 1040 Sandhill Road, Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL WIRING DIAGRAM,
 SWITCHED, PIPS**

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0983-13	1

SCALE: NONE SHEET 1 OF 1