


SERVER TECHNOLOGY, INC.
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	INITIAL DESIGN	1/16/2012	JSL/TI



POWER CORDS WITH NEUTRAL CONDUCTOR (WHITE) HAVE NEUTRAL CAPPED WITH NO INTERNAL CONNECTIONS.



Part Number	Expansion	Input	Output					
Master	Expansion	Rating, North America	Input Type	Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CS-18VD8454A3	CL-18VD8454A3	240V 3W+PE, 50/60Hz, 80A	IEC 60309	240V, 50/60Hz, <= 138.6A	18xC19 <= 16A each	IEC 60320 / C19	XY1, XY2, XY3, YZ1, YZ2, YZ3, ZK1, ZK2, ZK3 <= 20A	XY, YZ, ZK <= 46.2A
CS-18VD9454A3	CL-18VD9454A3	240V 3W+PE, 50/60Hz, 80A	Unterminated	240V, 50/60Hz, <= 138.6A	18xC19 <= 16A each	IEC 60320 / C19	XY1, XY2, XY3, YZ1, YZ2, YZ3, ZK1, ZK2, ZK3 <= 20A	XY, YZ, ZK <= 46.2A

ISO VIEW

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .130

ANGULAR DIMENSIONS:
 X = ± 1°
 XX = ± .5°
 XXX = ± .25°

SYMBOLS
 (G#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

MATERIAL:

FINISH:

SERVER TECHNOLOGY, INC.
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
 SMART CDU MODEL
 CL[CS]-18Vxx 208V, 3PH DELTA, 100A
 BASIC WIRING DIAGRAM

SIZE: B CAGE CODE: 049V0 DWG NO.: 495-0539-1 REV: 1

SCALE: NONE SHEET: 1 OF 1